


10 x 10mm Aperture, Quartz Lyot Depolarizer



Stock **#65-893** [CONTACT US](#)

-

1

+

₹52,160

ADD TO CART

Volume Pricing	
Qty 1-5	₹52,160 each
Qty 6+	₹42,117 each
Need More?	Request Quote

Product Downloads

General

Type:

Depolarizer

Physical & Mechanical Properties

Clear Aperture CA (mm):

10.0 x 10.0

Length (mm):

6.00

Dimensional Tolerance (mm):

±0.2

Crystalline	Construction:
<20	Parallelism (arcsec):
Optical Properties	
Crystal Quartz	Substrate: □
20-10	Surface Quality:
200 - 2300	Wavelength Range (nm):
λ/10	Surface Flatness (P-V):
Regulatory Compliance	
View	Certificate of Conformance:
China	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Lyot Depolarizers are not suitable for monochromatic light.
- Turn Polarized Light into Non-Polarized (Unpolarized) Light
 - Designed for Polychromatic Light
 - UV to IR Wavelength Range

Consisting of two quartz waveplates bonded together, Lyot Depolarizers are passive optical components that transform polarized or partially polarized light into non-polarized (unpolarized) light. The thickness ratio of the two waveplates is 2:1. They are positioned such that their optical axes are oriented 45° apart, creating various degrees of elliptically and linearly polarized light, and eliminating the polarization of the input beam.

Note: Lyot Depolarizers are not suitable for monochromatic light.

Lyot Depolarizers are designed for polychromatic light from 200 - 2300nm. Each Lyot Depolarizer features a minimum wavelength bandwidth of 50nm, which represents approximately 85% depolarization. A bandwidth of greater than 100nm is required for complete depolarization.

Technical Information

