


[See all 8 Products in Family](#)

TECHSPEC® 100 x 100mm High Transmission Linear Polarizing Film (XP44-40)



High Transmission Linear Polarizing Film (XP44-40)

Stock #19-020 CLEARANCE **13 In Stock**

⊖ 1 ⊕ MRP ₹6,155

📌 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹6,155 each
Need More?	Request Quote

Product Downloads

General

Linear Polarizer **Type:**

Note:
The polarisation axis is parallel to the notch on the polariser

Physical & Mechanical Properties

100.0 x 100.0 ±1 **Dimensions (mm):**

Thickness (mm):

0.40 ±0.05

Construction:

Polarizing Film

Optical Properties

Extinction Ratio:

2000:1

Substrate: □

[Polymer Film XP44-40](#)

Transmission (%):

Single: 44.2 ±1.5
Parallel: 38.6
Crossed: <0.02

Wavelength Range (nm):

400 - 700

Polarization Efficiency (%):

>99.95

Environmental & Durability Factors

Operating Temperature (°C):

-40 to +80

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 235:

[Contains SVHC\(s\)](#)

Country of Origin:

Japan

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Highest Transmission Polarizing Film for the Visible Spectrum
- >99.95% Polarization Efficiency
- Custom Options Available
- [High Contrast Linear Polarizing Film](#) Also Available

TECHSPEC® High Transmission Linear Polarizing Film (XP44-40) is optimized to offer the highest possible light transmission of a polymer film polarizer between 400 - 700nm. This linear polarizing film also features an excellent polarization efficiency of >99.95% in the visible spectrum. The polymer film sheets can be cut to custom sizes or laminated for increased stability to fit application requirements. TECHSPEC High Transmission Linear Polarizing Film is ideal for applications that require linear polarization with maximum light transmission, including machine vision or illumination applications.

Immediate Custom Quotes Available

If you have a need for anyround, square, or rectangular size of a TECHSPEC High Transmission Linear Polarizing Film (XP44-40) in dimensions between 3mm and 600mm, please visit our [Polarizing Film Tool](#). We'll provide an immediate quote, and can deliver the part to your requested size in approximately 3 weeks. A full list of standard manufacturing tolerances and restrictions are listed. For fully customized polymer polarizers to your requirements, visit our [Customized Polymer Polarizers Capabilities](#) page.