


TECHSPEC®

100 x 100mm High Transmission Linear Polarizing Film (XP44-40)



High Transmission Linear Polarizing Film (XP44-40)

Stock #19-020

CLEARANCE

15 In Stock

-

1

+

MRP ₹6,155

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-10	₹6,155 each
Qty 11+	₹5,518 each
Need More?	Request Quote

Product Downloads

General

Linear Polarizer

Type:

The polarisation axis is parallel to the notch on the polariser

Note:

Physical & Mechanical Properties

100.0 x 100.0 ±1

Dimensions (mm):

0.40 ±0.05	Thickness (mm):
Polarizing Film	Construction:
Optical Properties	
2000:1	Extinction Ratio:
Polymer Film XP44-40	Substrate: □
Single: 44.2 ±1.5 Parallel: 38.6 Crossed: <0.02	Transmission (%):
400 - 700	Wavelength Range (nm):
>99.95	Polarization Efficiency (%):
Environmental & Durability Factors	
-40 to +80	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 235:
Japan	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Highest Transmission Polarizing Film for the Visible Spectrum
 - >99.95% Polarization Efficiency
 - Custom Options Available
 - [High Contrast Linear Polarizing Film](#) Also Available
- TECHSPEC® High Transmission Linear Polarizing Film (XP44-40) is optimized to offer the highest possible light transmission of a polymer film polarizer between 400 - 700nm. This linear polarizing film also features an excellent polarization efficiency of >99.95% in the visible spectrum. The polymer film sheets can be cut to custom sizes or laminated for increased stability to fit application requirements. TECHSPEC High Transmission Linear Polarizing Film is ideal for applications that require linear polarization with maximum light transmission, including machine vision or illumination applications.

Immediate Custom Quotes Available

If you have a need for any round, square, or rectangular size of a TECHSPEC High Transmission Linear Polarizing Film (XP44-40) in dimensions between 3mm and 600mm, please visit our [Polarizing Film Tool](#). We'll provide an immediate quote, and can deliver the part to your requested size in approximately 3 weeks. A full list of standard manufacturing tolerances and restrictions are listed. For fully customized polymer polarizers to your requirements, visit our [Customized Polymer Polarizers Capabilities](#) page.