

[See all 5 Products in Family](#)

Coherent® High Sensitivity Optical Power Sensor 1098318 | 1000:1 Attenuator

See More by [Coherent®](#)



#59-970 Coherent® High Sensitivity Optical Power Sensor 1098318 | 1000:1 Attenuator

Stock **#59-970** **1 In Stock**

MRP ₹59,472

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹59,472 each
Need More?	Request Quote

Product Downloads

General

Calibration Uncertainty (%):
±5

Compatible Laser Models:
[#59-979](#) and [#59-980](#)

Optical Properties

Wavelength Range (nm):
400 - 1800

Min. to Max. Attenuation:

Electrical

Maximum Incident Power Density (mW/cm²):
100

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Reach 224:
[Compliant](#)

Certificate of Conformance:
[View](#)

Country of Origin:
United States

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Utilize Silicon or Germanium Detectors
- Ideal for nW to Low mW CW Laser Measurements
- Removable Light Shield
- Compatible with [Coherent® Laser Power and Energy Meters](#)

Coherent® High Sensitivity Optical Power Sensors are semiconductor sensors designed for nanowatt to low milliwatt continuous wave laser measurements. These semiconductor sensors are available for detection from the ultraviolet to the infrared, and feature a removable light shield. An attenuator is also available that will boost power up to 5W.

Note: OP-2 sensors are compatible with the LabMax-Pro ([#35-203](#)), LabMax-TOP/TO ([#88-412](#)), FieldMaxII-TOP/TO ([#66-277](#)), and FieldMate ([#59-978](#)) meters.