

[See all 30 Products in Family](#)

TECHSPEC<sup>®</sup> 10.0mm 320 - 450nm, N-BK7 Right Angle Mirrors (Hypotenuse Coated)



Broadband Dielectric Coated Right Angle Mirrors

Stock **#15-594** 2 In Stock

-

1

+

₹12,145

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹12,145 each                  |
| Qty 6-25       | ₹9,731 each                   |
| Qty 26-49      | ₹9,108 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Right Angle Mirror

Type:

Physical & Mechanical Properties

90

Clear Aperture (%):

±0.1

Dimensional Tolerance (mm):

|                                                                                                                                                                                                                                |                                                       |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------|
| 14.10                                                                                                                                                                                                                          | Length of Hypotenuse (mm):                            |
| 10.00                                                                                                                                                                                                                          | Length of Legs (mm):                                  |
| Optical Properties                                                                                                                                                                                                             |                                                       |
| Dielectric                                                                                                                                                                                                                     | Coating Type:                                         |
| Dielectric Mirror (320-450nm)                                                                                                                                                                                                  | Coating:                                              |
| 320 - 450                                                                                                                                                                                                                      | Wavelength Range (nm):                                |
| N-BK7                                                                                                                                                                                                                          | Substrate: <input type="checkbox"/>                   |
| ±2                                                                                                                                                                                                                             | Angle Tolerance (arcmin):                             |
| Coating Specification:<br>Hypotenuse: R <sub>avg</sub> >98% @ 340 - 488nm (0°, All Polarizations)<br>R <sub>avg</sub> >98% @ 320 - 450nm (45°, All Polarizations)<br>R <sub>avg</sub> >99% @ 320 - 450nm (45°, S-Polarization) |                                                       |
| 40-20                                                                                                                                                                                                                          | Surface Quality:                                      |
| 0.5 J/cm2 @ 355nm, 20ns, 20Hz                                                                                                                                                                                                  | Damage Threshold, By Design: <input type="checkbox"/> |
| 1.25                                                                                                                                                                                                                           | Power (fringes) @ 632.8nm:                            |
| 0.50                                                                                                                                                                                                                           | Irregularity (fringes) @ 632.8nm:                     |
| Regulatory Compliance                                                                                                                                                                                                          |                                                       |
| View                                                                                                                                                                                                                           | Certificate of Conformance:                           |
| United States                                                                                                                                                                                                                  | Country of Origin:                                    |
| Edmund Optics India Private Limited                                                                                                                                                                                            | Imported By:                                          |

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Greater Than 98% Reflection Over Broad Wavelength Ranges
- High Reflectivity for all Polarization States
- Reflect Light at 90°
- [Standard Metal Coated Right Angle Mirrors](#) Also Available

TECHSPEC® Broadband Dielectric Coated Right Angle Mirrors (Hypotenuse Coated) are designed for beam steering or precision alignment applications utilizing multiple laser sources or operating from the visible to near-infrared spectra. These mirrors feature improved reflection compared to standard metal coated mirrors, increasing system performance by decreasing energy loss. These right angle mirrors are easily mounted and integrated into optical systems. TECHSPEC® Broadband Dielectric Coated Right Angle Mirrors (Hypotenuse Coated) reflect light at 90° and have greater than 98% reflection over broad wavelength ranges. These mirrors feature a N-BK7 substrate and are available in a variety of leg lengths.

**Note:** These right angle mirrors are not recommended for use in applications where light is reflected off the coated hypotenuse from inside the prism.

## Technical Information



Image above shows light reflecting off the coated hypotenuse.