

# 100mm Cobra Max White Line Light



100mm Cobra MaxLine Light



Stock **#73-944** [CONTACT US](#)

⊖ 1 ⊕ MRP ₹2,55,411

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹2,55,411 each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

### General

**Type of Illumination:**  
LED

**Note:**  
Lights are fan cooled. See datasheet for additional mounting, spectral, and irradiance information

**Manufacturer:**  
ProPhotonix

Line Light **Geometry:**

Ethernet Controlled, Continuous **Illumination Mode:**

## Physical & Mechanical Properties

100.00 **Length (mm):**

100.00 x 173.50 **Dimensions (mm):**

Collimated (M2) **Lens Position:**

## Optical Properties

White **Color:**

10-61 **Working Distance (mm):**

## Hardware & Interface Connectivity

Straight **Connector:**

24 **Operating Voltage (V):**

Power supply required and sold separately. USA  
[#73-977](#) **Power Supply:**

2m braided power cable included **Length of Cable (m):**

## Threading & Mounting

Aluminum T-Slot Extrusion **Mount:**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

Ireland **Country of Origin:**

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000 **Imported By:**

## Product Details

- Intensities up to 3140kLux
- 100, 300, or 600mm Length Options Available
- White, Red, Multispectral, and SWIR Illumination Options Available

ProPhotonix COBRA™ MAXLED Line Lights are slim, compact LED line lights available in lengths of 100, 300, or 600mm in red, white, multispectral, or SWIR illumination options. These line lights feature Chip-on-Board LED technology which offers greater uniformity, thermal performance, and intensity while maintaining a compact size compared to traditional surface mount LED constructions. ProPhotonix COBRA™ MAXLED Line Lights multispectral option offers RGB-IR illumination and the ability to control each wavelength independently. The available easy-to-use comprehensive software package can be customized to meet specific application needs and is downloadable from a QR code included with the units. These lights are ideal for many linescan inspection applications such as solar cell inspection, semiconductor inspection, food sorting, and flat panel display inspection.

**Note:** Required 24V Power Supply, [#73-977](#), sold separately. Optional Lens Kits are available to adjust the working distance by changing the position of the projection lens.