

[See all 8 Products in Family](#)

## 100mm Dia x 12.5mm FL Alum. Coated, Parabolic Reflector



Stock #90-964 **2 In Stock**

- 1 + MRP ₹40,961

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-10	₹40,961 each
Qty 11-25	₹36,119 each
Qty 26-49	₹34,001 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Parabolic Mirror **Type:**

### Physical & Mechanical Properties

100.00 +0.0/-0.5 **Diameter (mm):**

No Center Hole **Center Hole Diameter (mm):**

48.2 ±0.5	<b>Height (mm):</b>
<b>Optical Properties</b>	
Metal	<b>Coating Type:</b>
Protected Aluminum (400-700nm)	<b>Coating:</b>
400 - 700	<b>Wavelength Range (nm):</b>
<a href="#">BOROFLOAT®</a>	<b>Substrate:</b> <input type="checkbox"/>
0.125	<b>Aperture (f#):</b>
R <sub>avg</sub> >85% @400 - 700nm	<b>Coating Specification:</b>
12.50	<b>Focal Length FL (mm):</b>
<b>Regulatory Compliance</b>	
<a href="#">View</a>	<b>Certificate of Conformance:</b>
Japan	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>


## Product Details

- Precision Polished Substrate
- Protected Aluminum and Cold Mirror Coating Options
- Ideal for Highly Divergent Light Sources
- [Precision Ellipsoidal Reflectors](#) Also Available


Precision Parabolic Reflectors are ideal for collimating a light source placed at the focal point of the mirror. The parabolic profile eliminates spherical aberration, allowing the light source to maintain its wavefront characteristics. These Precision Parabolic Reflectors feature very low *f*/#s, making them ideal for highly divergent light sources. The protected aluminum coating features broadband high reflection through the visible and IR spectra. The cold mirror coating reflects visible light while transmitting NIR, making it ideal for cold condensing applications.

Precision Parabolic Reflectors are precision polished, yielding exact aspheric profiles. These mirrors offer improved thermal stability and superior focusing efficiency versus commercially available press-molded reflectors. Typical applications include use as steppers for PCB, LCD, or PDP production, solar simulators, fiber optic illuminators, and projectors.

## Technical Information



Diameter	Focal Length f	Center Hole Diameter d	Height H	Stock No.
100mm	12.5mm	—	45mm	<a href="#">#90-964</a>
		—	—	<a href="#">#90-967</a>
	19mm	30mm	32mm	<a href="#">#68-791</a>
		—	—	<a href="#">#68-795</a>
152mm	17mm	30mm	79mm	<a href="#">#68-792</a>
	30mm	35mm	47mm	<a href="#">#90-965</a>
220mm	100mm	—	33mm	<a href="#">#68-793</a>
300mm	42mm	—	130mm	<a href="#">#90-966</a>



;