

[See all 6 Products in Family](#)

TECHSPEC® 100mm, f/4 Athermal Lens



Stock **#16-849** [CONTACT US](#)

1 [-](#) [+](#) MRP ₹1,72,347

! Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹1,72,347 each
Need More?	Request Quote

Product Downloads

General

Athermal Series **Product Family:**

Fixed Focal Length Lens - Athermal **Type:**

Passive Athermalization and Mechanical Ruggization **Imaging Lens Type:**

Physical & Mechanical Properties

Fixed	Iris Option:
94.90	Length (mm):
40.0	Maximum Diameter (mm):
40	Outer Diameter (mm):

Optical Properties

Horizontal: 8.01° Vertical: 6.03° Diagonal: 9.96°	Field of View at Max Sensor Format:
8.01°	Horizontal Field of View, 1.1" Sensor:
7.30°	Horizontal Field of View, 1" Sensor:
5.04°	Horizontal Field of View, 2/3" Sensor:
4.12°	Horizontal Field of View, 1/1.8" Sensor:
3.67°	Horizontal Field of View, 1/2" Sensor:
19.30	Maximum Image Circle (mm):
0.003	Numerical Aperture NA, Object Side:
7 (3)	Number of Elements (Groups):
100.00	Focal Length FL (mm):
0.000X - 0.026X	Primary Magnification PMAG:
4000 - ∞	Working Distance (mm):
f/4	Aperture (f/#):
10.85	Entrance Pupil Position (mm):
-51.57	Object Space Principal Plane (mm):
-20.08	Image Space Principal Plane (mm):
1.21	Maximum Distortion (%):
-21.381	Exit Pupil Position (mm):
VIS	Lens Wavelength Range:

Sensor

1.2"	Maximum Sensor Format:
2.74	Pixel Size (µm):

Threading & Mounting

M35.5 x 0.50 (Female)	Filter Thread:
C-Mount	Mount:

Environmental & Durability Factors

-10 to +50	Operating Temperature (°C):
Athermal	Type of Ruggedization:

Regulatory Compliance

View	Certificate of Conformance:
United States	Country of Origin:

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details


- Designed to Maintain High Resolution Over a Wide Temperature Range
- Ruggedized for Shock and Vibration Environments
- Large Sensor Coverage up to 1.1"
- Optothermal Stability from [Passive Athermalization](#)
- [2022 Silver VSD Innovators Award Winner](#) and 2022 Inspect Award Winner

TECHSPEC® Athermal Imaging Lenses provide optothermal stability in a ruggedized lens housing, making them ideal for harsh environments. These lenses utilize [passive athermalization](#) to mitigate the effects of thermal defocus in applications that are prone to temperature fluctuations. Additionally, these lenses are ruggedized to protect against lens damage and minimize pixel shift after shock and vibration. Along with being ruggedized to protect against lens damage and minimize pixel shift after shock and vibration, these lenses are thermally compensated and best used with camera mounts made from aluminum. TECHSPEC® Athermal Imaging Lenses feature C-Mount threading and full coverage of sensors up to 1.1".


These lenses won the [2022 Silver VSD Innovators Award](#) and the 2022 Inspect Award.

Note: Passive Athermalization is introduced in the application note [here](#).


Technical Information




#16-849, 100mm, f/4 Athermal Lens, Distortion Plot




#16-849, 100mm, f/4 Athermal Lens, Relative Illumination Plot




#16-849, 100mm, f/4 Athermal Lens, Working Distance versus Field of View Plot



#16-849, 100mm, f/4 Athermal Lens, Modulated Transfer Function (MTF) Plot, 4000mm Working Distance, f4



#16-849, 100mm, f/4 Athermal Lens, Depth of Field Plot, 100000mm Working Distance, f4



#16-849, 100mm, f/4 Athermal Lens, Modulated Transfer Function (MTF) Plot, Working Distance: Infinity, f4

Compatible Cameras