

[See all 96 Products in Family](#)

## 100µm Aperture Diameter, Unmounted, Precision Pinhole



Unmounted Precision Pinhole

Stock #36-392 **20+ In Stock**

MRP ₹7,315

**Price inclusive of all taxes**

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹7,315 each
Qty 6-10	₹6,497 each
Qty 11+	₹6,013 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Unmounted **Type:**

### Physical & Mechanical Properties

9.5 **Outer Diameter (mm):**

**Construction:**

Stainless Steel

Fixed Aperture Diameter ( $\mu\text{m}$ ):

100

Thickness (mm):

0.03 Nominal

Aperture Tolerance ( $\mu\text{m}$ ):

$\pm 5$

Aperture Centration ( $\mu\text{m}$ ):

$\pm 50$

## Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 247:

Compliant

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Available in Aperture Mounts for a Secure Mechanical Support
- Pinhole Sized Ranging from 1 to 1,000 Microns
- [High Power Apertures](#) Available

### Unmounted Precision Pinholes

Precision Pinholes are high quality apertures centered to  $\pm 0.002''$  (50 microns). They are constructed of stainless steel and are  $3/8''$  (9.5mm) in diameter. Smaller diameter pinholes will reduce energy throughput, while larger diameter pinholes will pass more spatial noise. Precision pinholes have sizes ranging from 1 to 1,000 microns. Typical applications include leak detection, aerosol studies, holography, fiber optics guides, spatial filtering, research, and more.

Use the [Precision Pinhole Mount](#) to integrate unmounted pinholes into a variety of mechanical components easily.

### Mounted Precision Pinholes

Precision Pinholes are available in aperture mounts for secure mechanical support. The mounts also fit into various optical assemblies. Each 9.5mm diameter pinhole is sealed within a 25mm diameter black-anodized aluminum mount. The mount is clearly labeled with a pinhole aperture diameter for easy identification.

**Note:** Aperture Centering to Mount  $\pm 125$  microns.

Edmund Optics offers a wide selection of precision pinholes for leak detection, aerosol studies, holography, fiber optic guides, spatial filtering, research, and more. These pinholes are available in a range of diameters and are ideal for controlling light propagation. Each pinhole is manufactured using high-accuracy techniques, providing consistent circular aperture geometry and high edge quality. Available in both mounted and unmounted formats, these pinholes support a variety of optical setups, from experimental labs to industrial environments.

## Technical Information

