

[See all 5 Products in Family](#)

101 x 127mm, Extended Hot Mirror



Extended Hot Mirrors

Stock **#47-304** **9 In Stock**

⊖ 1 ⊕ ₹21,097

ADD TO CART

Volume Pricing	
Qty 1-9	₹21,097 each
Qty 10-25	₹18,995 each
Qty 26-49	₹18,061 each
Need More?	Request Quote

Product Downloads

General

Shortpass Filter **Type:**

Physical & Mechanical Properties

101.0 x 127.0 **Dimensions (mm):**

3.30 ±0.2 **Thickness (mm):**

±0.5 Dimensional Tolerance (mm):

≥85 Clear Aperture (%):

Seamed Edges:

Optical Properties

0.00 Angle of Incidence (°):

Hot Mirror, 0° Coating:

BOROFLOAT® Substrate:

80-50 Surface Quality:

Coating Specification:
R_{avg} ≥90% @ 750 - 1150nm
R_{avg} ≥80% @ 1200 - 1600nm
T_{avg} ≥85% @ 425 - 675nm

425 - 1600 Wavelength Range (nm):

4 - 6λ Surface Flatness (P-V):

Dielectric Coating Type:

Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Compliant Reach 247:

United States Country of Origin:

Edmund Optics India Private Limited Imported By:



Product Details

- Improved NIR Reflectance Over Standard Hot Mirrors
- Operating Temperatures up to 230°C
- Neutral Color for 5500K or 3200K Sources to ±250K

Extended Hot Mirrors are designed to reduce the heat in an optical system without sacrificing the system's visible output. While typical hot mirrors reflect from 750nm to approximately 1250nm, Extended Hot Mirrors further reduce heat by extending the reflection range to approximately 1750nm.

Hot mirrors are crucial in many projection and illumination systems where high levels of heat can quickly damage sensitive components. Hot mirrors are specially coated to transmit visible light while reflecting the NIR, a major contributor to heat generation. By using a hot mirror, heat levels are limited with minimum impact on the overall system performance.

Technical Information



Quote Your Size

Compatible Mounts
