

[See all 7 Products in Family](#)

1030nm, 0.80 NA, aplanoXX Aplan Objective | aplanoXX NA0.8_20_1030

See More by [AdlOptica](#)



AdlOptica aplanoXX Aplan Objectives



Stock #19-491 **1 In Stock**

MRP ₹9,11,879

● Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹9,11,879 each
Need More?	Request Quote

Product Downloads

General

aplanoXX NA0.8_20_1030 **Model Number:**

Objective **Type:**

±0.3 **Field of View (°):**

Note:

Includes aplanoXX objective, mounted protective window (#19-495), and spanner wrench (#19-497)

Physical & Mechanical Properties

54.10 **Length (mm):**

20 **Clear Aperture CA (mm):**

44.00 **Diameter (mm):**

Optical Properties

12.50 **Focal Length FL (mm):**

0.80 **Numerical Aperture NA:**

2.5 (1.6 with Protective Window) **Working Distance (mm):**

1030 **Design Wavelength DWL (nm):**

1020 - 1100 **Wavelength Range (nm):**

100 mJ @ 5ns
300 μJ @ 1ps **Damage Threshold, By Design:** □

0 - 4 **Focusing Depth (mm):**

20 (maximum) **Beam Diameter (mm):**

100 mJ @ 5ns
300 μJ @ 1ps **Damage Threshold, Pulsed:**

Threading & Mounting

C-Mount **Mount:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 250:**

Germany **Country of Origin:**

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000 **Imported By:**

Product Details

- Aplanatic Optical Design
- High Numerical Aperture for Small Spot Sizes
- Designs for 800 and 1030nm with Focusing Depth Up to 4mm
- [AdlOptica foXXus Multi-Focus Objectives](#) Also Available

AdlOptica aplanoXX Aplan Objectives compensate for spherical aberration and coma when focusing into glass, sapphire, silicon carbide, silicon, PMMA, and other transparent materials at depths up to 4mm. These objectives are designed to be used with ultrafast solid-state and fiber lasers and are optimized for 800nm (Ti:sapphire) and 1030nm (Yb:doped). Featuring C-Mount threading and an optical design insensitive to misalignment, these objectives are easy to integrate into laser systems. AdlOptica aplanoXX Aplan Objectives are ideal for micromachining glass, 3D nanofabrication, waveguide recording, and selective laser etching. A collar on the objective allows for manual adjustment of focus and a replaceable front window protects from debris during materials processing.

Technical Information

