


[See all 4 Products in Family](#)

TECHSPEC® 1030nm, 12.7mm Dia., 45° Thin Film Polarizer



TECHSPEC® Ultrafast Thin Film Polarizers

Stock #13-055 **20+ In Stock**

1 MRP ₹37,633

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-4	₹37,633 each
Qty 5-9	₹33,294 each
Qty 10+	₹29,460 each
Need More?	Request Quote

Product Downloads

General

Linear Polarizer **Type:**

Physical & Mechanical Properties

12.70 +0.00/-0.10 **Diameter (mm):**

Thickness (mm):

3.00 ±0.10

<3 **Parallelism (arcmin):**

85 **Clear Aperture (%):**

Optical Properties

45 ±1 **Angle of Incidence (°):**

Thin Film Polarizer (1030nm) **Coating:**

1030 **Design Wavelength DWL (nm):**

1000:1 **Extinction Ratio:**

Fused Silica (Corning 7980) **Substrate:**

10-5 **Surface Quality:**

M10 @633nm **Transmitted Wavefront, P-V:**

Coating Specification:
S1: R_s >99.8% @ 1030nm, T_p >98% @ 1030nm
S2: R_p <0.1% @ 1030nm

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Lithuania **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Ideal for Ti:sapphire and Yb:doped Ultrafast Lasers
- Optimized for Separation of S and P Polarizations at 45° AOI
- High Extinction Ratio of 1000:1 @DWL

TECHSPEC® Ultrafast Thin Film Polarizers utilize thin film coating technology to achieve optimal performance at 800 and 1030nm. The ion beam sputtering (IBS) coating on these polarizers provides >99.8% reflectance of the s-polarization and >98% transmission of the p-polarization at a 45° angle of incidence. TECHSPEC Ultrafast Thin Film Polarizers are ideal to use with ultrafast laser sources such as Ti:sapphire and Yb:doped lasers. Please contact us if your application requires an Ultrafast Thin Film Polarizer with a custom size or coating specifications.

Note: The arrow on the edge of these optics points towards the thin film polarizer coating.

Coating Curves