

[See all 102 Products in Family](#)

## 10.5mm Diameter x 9.45mm FL, MgF<sub>2</sub> Coated, Aspheric Condenser Lens



Stock **#15-530** **1 In Stock**

[Other Coating Options](#)

1  MRP ₹6,406

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-10	₹6,406 each
Qty 11-49	₹5,751 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Condenser Lens **Type:**

### Physical & Mechanical Properties

10.50 +0.00/-0.15 **Diameter (mm):**

≤30 **Centering (arcmin):**

9.8	Clear Aperture CA (mm):
1.1	Edge Thickness ET (mm):
3.80 ±0.2	Center Thickness CT (mm):
Protective as needed	Bevel:
10.5	Diameter of Asphere (mm):
Plano	Shape of Back Surface:

## Optical Properties

9.45	Effective Focal Length EFL (mm):
0.56	Numerical Aperture NA:
8.10	Back Focal Length BFL (mm):
<a href="#">N-F2</a>	Substrate: <input type="checkbox"/>
±7	Focal Length Tolerance (%):
MgF <sub>2</sub> (400-700nm)	Coating:
R <sub>avg</sub> ≤ 1.75% @ 400 - 700nm	Coating Specification:
80-50 (typical)	Surface Quality:
0.9	f/#:
36.43	Abbe Number (v <sub>d</sub> ):
1.620	Index of Refraction (n <sub>d</sub> ):
Plano	Radius R <sub>2</sub> (mm):
400 - 700	Wavelength Range (nm):
Infinite	Conjugate Distance:

## Material Properties

7.8	Coefficient of Thermal Expansion CTE (10 <sup>-6</sup> /°C):
-----	--

## Regulatory Compliance



<a href="#">Compliant</a>	RoHS 2015:
<a href="#">View</a>	Certificate of Conformance:
<a href="#">Compliant</a>	Reach 235:
Germany	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

## Product Details

- Molded Illumination Lenses
- Aspheric or Spherical Designs
- High Numerical Apertures

Condenser Lenses are molded lenses designed for illumination applications. Featuring large apertures and short focal lengths, Condenser Lenses are commonly used in emitter-detector applications, projection applications, or condensing illumination applications such as Koehler Illumination. The Aspheric Condenser Lenses are molded on the aspheric surface and ground and polished on the opposite face, offering superior performance. The Plano-Convex (PCX) Condenser Lenses are molded on both surfaces, offering excellent value.

## Technical Information



## Coating Curves