


[See all 21 Products in Family](#)

1.05 μ m, 12.5mm Diameter, Infrared Longpass Filter



Infrared (IR) Longpass Filters

Stock #33-967 **6 In Stock**

1 MRP ₹18,867

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-9	₹18,867 each
Qty 10-25	₹16,950 each
Qty 26-49	₹16,042 each
Need More?	Request Quote

Product Downloads

General

Longpass Filter **Type:**

Note:
Transmission at cut-on wavelength is 5% of peak transmission.

Physical & Mechanical Properties

12.50 +0.0/-0.1	Diameter (mm):
1.00 ±0.2	Thickness (mm):
<10	Parallelism (arcmin):
90	Clear Aperture (%):

Optical Properties

≥3.0	Optical Density OD (Average):
1,050.00	Cut-On Wavelength (nm):
Silicon (Si)	Substrate: <input type="checkbox"/>
Traditional Coated	Coating:
80-50	Surface Quality:
>85 (average)	Transmission (%):
1100 - 2100	Transmission Wavelength (nm):
1.10 - 2.10	Transmission Wavelength (μm):
200 - 1050	Blocking Wavelength Range (nm):
<12	Slope Factor (%):
1.05 ±0.04	Cut-On Wavelength (μm):
3 - 5λ	Surface Flatness (P-V):

Environmental & Durability Factors

-62 to +71	Operating Temperature (°C):
------------	------------------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:


Product Details

- Coated on Silicon or Germanium Substrates
- Ideal for Isolating Broad Spectral Regions
- Durable, First-Surface Coatings

• **Due to material supply chain disruptions with germanium, there may be increased lead times and price changes on our germanium products. For more information, please contact our customer service team.**

Infrared (IR) Longpass Filters provide a sharp cut-off below a particular wavelength. Often used for order sorting, they isolate broad regions of the spectrum, simultaneously providing high transmission of desired energy, and deep rejection of unwanted energy. These filters are constructed of hard, durable first-surface dielectric coatings on optical-quality IR-transmitting substrates. Infrared (IR) Longpass Filters are able to withstand normal cleaning and handling associated with any high-quality optical component because of their make-up. These filters are particularly useful for FTIR spectroscopy and Thermal Imaging Applications. For custom sizes and coating requirements, please contact our [Sales Department](#).

Technical Information



Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

Compatible Mounts