


[See all 32 Products in Family](#)

1064nm, 15-20mm Dia. Input Beam, Focal Flat Top Beam Shaper | Focal πShaper_1064_Q-17

See More by [AdiOptica](#)



Focal Flat Top Beam Shaper



Stock #12-236 **1 In Stock**

1 MRP ₹3,35,516

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-4	₹3,35,516 each
Qty 5-10	₹3,01,582 each
Qty 11+	₹2,85,332 each
Need More?	Request Quote

Product Downloads

General

Model Number:
πShaper_1064_Q-17

Beam Shaper **Type:**

Compatible Adapter:
#12-323

Physical & Mechanical Properties

Length (mm):
21.00

Weight (g):
70

Clear Aperture CA (mm):
38

Diameter (mm):
64.00

Input Beam Diameter, $1/e^2$ (mm):
15 - 20

Optical Properties

Transmission (%):
>99

Design Wavelength DWL (nm):
1064

Wavelength Range (nm):
1020 - 1100

Input Beam Mode:
TEM₀₀

Typical Input Beam Mode Quality, M²:
<1.5

Input Beam Divergence (mrad):
±20

Electrical

Maximum Input Power, CW (kW):
0.4

Threading & Mounting

Inner Thread:
M58 x 1

Outer Thread:
M58 x 1

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 250:
[Compliant](#)

Country of Origin:
Germany

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000

Product Details

- Shapes Gaussian Beams to Airy Disk Profile
- Airy Disk is Focusable to Flat Top Spot
- Near 100% Efficiency
- [AdlOptica πShaper Flat Top Beam Shapers](#) Also Available

AdlOptica Focal-πShaper (piShaper) Q Flat Top Beam Shapers are used to transform Gaussian beams to flat-top profiles after focusing through a lens. This is accomplished by transforming the Gaussian beam to airy disk profiles immediately after the piShaper. These beam shapers feature a compact design with inner and outer threading, making them easy to integrate into equipment. AdlOptica Focal-πShapers are advantageous for beam shaping in micromachining applications, including scribing and PCB drilling, as well as micro-welding applications. Multiple models are available at Nd:YAG, Ti:Sapphire, and Infrared wavelengths with compatible input beam diameters as small as 2.5mm and up to 23mm.

Technical Information

