

TECHSPEC® 1064nm, 25mm Diameter, Thin Film Laser Line Polarizer



TECHSPEC High Energy Laser Line Polarizers

Stock **#86-716** **3 In Stock**

MRP ₹57,507

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹57,507 each
Qty 6-25	₹51,454 each
Need More?	Request Quote

Product Downloads

General

Linear Polarizer **Type:**

Physical & Mechanical Properties

22.50 **Clear Aperture CA (mm):**

25.00 **Diameter (mm):**

6.00 ±0.25 **Thickness (mm):**

+0.00/-0.25 **Dimensional Tolerance (mm):**

Thin Film Dielectric **Construction:**

90 **Clear Aperture (%):**

Optical Properties

45 ±2 **Angle of Incidence (°):**

1064 **Design Wavelength DWL (nm):**

10,000:1 **Extinction Ratio:**

[Fused Silica](#) (Coming 7980) **Substrate:**

40-20 **Surface Quality:**

>98 (P-Polarization) **Transmission (%):**

M4 @ 633nm **Transmitted Wavefront, P-V:**

2 J/cm² @ 532nm, 10ns, S or P Polarization **Damage Threshold, By Design:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 247:**

United States **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- High Extinction Ratio of 10,000:1
- 45° Angle of Incidence
- Available for Nd:YAG Harmonics and HeNe Wavelengths

TECHSPEC® Thin Film Laser Line Polarizers are used to transmit P-polarized light while reflecting S-polarized light. These polarizers with thin film dielectric coatings combine high laser damage thresholds with high extinction ratios for optimal performance in a range of laser applications. The UV grade fused silica substrate maximizes performance, while the hard anti-reflection coating makes these durable polarizers easy to clean and simple to align. TECHSPEC® Thin Film Laser Line Polarizers have an 45° angle of incidence. The polarizers are available for common laser wavelengths.

LASER OPTICS MADE BY EDMUND OPTICS®

[LEARN MORE](#)