

[See all 14 Products in Family](#)

## 1064nm CWL, 2.00 FWHM, 25mm Dia.Ultra Narrow Filter



Stock #21-395 **3 In Stock**

- 1 + MRP ₹1,66,469

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹1,66,469 each
Qty 6-25	₹1,49,822 each
Qty 26-49	₹1,42,356 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Bandpass Filter **Type:**  
Filter Design: Two-Cavity **Note:**

#### Physical & Mechanical Properties

25.00 +0.00/-0.25 **Diameter (mm):**

21.00	<b>Clear Aperture CA (mm):</b>
6 +0.00/-0.25	<b>Substrate Thickness (mm):</b>
<b>Optical Properties</b>	
0	<b>Angle of Incidence (°):</b>
1,064.00	<b>Center Wavelength CWL (nm):</b>
2.00	<b>Full Width-Half Max FWHM (nm):</b>
Soda Lime Glass & Filter Glass	<b>Substrate:</b> <input type="checkbox"/>
>70	<b>Minimum Transmission (%):</b>
<b>Regulatory Compliance</b>	
<b>Compliant</b>	<b>RoHS 2015:</b>
<b>View</b>	<b>Certificate of Conformance:</b>
<b>Compliant</b>	<b>REACH 241:</b>
United States	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Bandwidths Between 0.2 and 5.0nm
- OD 4.0 Blocking Between 200 and 1200nm
- Rapid Custom Designs Available
- [Ultra Narrow Hard Coated Bandpass Filters](#) Also Available

Ultra Narrow Traditional Coated Bandpass Filters are ideal for use as laser line, laser cleanup, or laser excitation filters in demanding medical and laser applications. These filters provide OD 4 blocking by design, center wavelength tolerances as tight as 0.05nm, and bandwidths ranging from 0.2nm to 5.0nm. Multiple standard wavelength options including H-alpha hydrogen, HeNe laser, and Nd:YAG laser line are available. Rapid custom filters with bandwidth between 0.15 and 50nm and center wavelength between 340 and 2400nm are available. Please [contact us](#) for a quote.