

[See all 25 Products in Family](#)

1070nm Dual Stage Free-Space Optical Isolator



1070nm Dual Stage Free-Space Optical Isolator, #35-988

Stock **#35-988** [CONTACT US](#)

1 MRP ₹5,35,726

Price inclusive of all taxes

[ADD TO CART](#)

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1-4 | ₹5,35,726 each |
| Qty 5+ | ₹4,82,154 each |
| Need More? | Request Quote |

Product Downloads

General

Dual Stage Optical Isolator **Type:**
Faraday **Style:**

Physical & Mechanical Properties

4.7 **Clear Aperture CA (mm):**

Optical Properties

80 **Minimum Transmission (%)**:

90 (typical) **Transmission (%)**:

1070 **Design Wavelength DWL (nm)**:

1050 - 1100 **Wavelength Range (nm)**:

40 W, 4 kW/cm² @ DWL **Damage Threshold, By Design:** □

67 **Typical Isolation at Design Wavelength (dB)**:

60 **Minimum Isolation at Design Wavelength (dB)**:

40 W, 4 kW/cm² @ DWL **Damage Threshold, CW:**

Environmental & Durability Factors

+15 to +40 **Operating Temperature (°C)**:

Regulatory Compliance

[View](#) **Certificate of Conformance:**

United States **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Up to 67 dB Isolation for Ultimate Stability
- Up to 92% Transmission for Maximum Power
- 4.7mm Input Aperture

Free-Space Optical Isolators incorporate a Faraday Rotator and are specifically designed and manufactured to provide superior performance with high isolation, transmission, and power densities. Each option effectively reduces feedback in the external cavity of diode laser systems and blocks reflections from free-space fiber coupling. Free-Space Optical Isolators increase power stabilization in optical systems and also eliminate feedback-induced damage to sensitive optical components. These isolators enable state of the art protection for the most stable lasers in the world and are ideal for demanding laser applications.

LASER OPTICS MADE BY EDMUND OPTICS®

[LEARN MORE](#)