


[See all 3 Products in Family](#)

TECHSPEC® 10mm Aluminized, Schmidt Prism



Stock #47-259 **20+ In Stock**

1 MRP ₹20,582

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹20,582 each
Qty 6-25	₹16,546 each
Qty 26-99	₹15,437 each
Need More?	Request Quote

Product Downloads

General

Schmidt Prism **Type:**

Physical & Mechanical Properties

16.5 **Height (mm):**

14.70 **Length (mm):**

±0.1	Dimensional Tolerance (mm):
Protective as needed	Bevel:
10.00	Width (mm):
Optical Properties	
MS 0° & Aluminized	Coating:
N-BK7	Substrate: <input type="checkbox"/>
40-20	Surface Quality:
5.00	Angle Tolerance (arcmin):
Right-Handed	Image Orientation:
Coating Specification: Entrance/Exit Faces: R _{avg} ≤0.4% @ 425 - 675nm Roof: R _{avg} >85% @ 400 - 700nm w/Black Overpaint	
45	Ray Deviation (°):
400 - 700	Wavelength Range (nm):
1.00	Power (fringes) @ 632.8nm:
0.25	Irregularity (fringes) @ 632.8nm:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 233:
Singapore	Country of Origin:
Imported By: Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).




Product Details

- Ray Deviation of 45°
- Right Handed Image
- 5 Arcsecond Roof Angle Tolerance
- Combine with Half-Penta Prism to Create Schmidt-Pechan Prism

Schmidt prisms are ideal for creating a right handed image with a ray deviation of 45°. They are similar in function to [TECHSPEC® Amici Roof Prisms](#), however the 45° deviation makes Schmidt prisms especially useful in eyepiece assemblies and imaging systems requiring a path bend. The aluminized roof surfaces enhance the overall efficiency while the 5arcsecond roof angle tolerance increases the prism's resolution. TECHSPEC® Schmidt Prisms can be combined with [TECHSPEC® Half-Penta Prisms](#) to create a Pechan prism.

Technical Information

#47-259



;