

[See all 8 Products in Family](#)

TECHSPEC® 10mm Dia., 1mm Thick, Uncoated, Lithium Fluoride (LiF) Window



Lithium Fluoride (LiF) Windows

Stock #19-725 **9 In Stock**

1 MRP ₹17,757

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-10	₹17,757 each
Qty 11-25	₹15,941 each
Qty 26-49	₹15,134 each
Need More?	Request Quote

Product Downloads

General

Protective Window **Type:**

Crystal **Type of Window:**

Physical & Mechanical Properties

Clear Aperture CA (mm):

9.00	
10.00 +0.00/-0.10	Diameter (mm):
1.00 ±0.10	Thickness (mm):
<3	Parallelism (arcmin):
Protective as needed	Bevel:
90	Clear Aperture (%):
Fine Ground	Edges:
0.33	Poisson's Ratio:
64.97	Young's Modulus (GPa):
102.00	Knoop Hardness (kg/mm²):

Optical Properties

Uncoated	Coating:
Lithium Fluoride (LiF)	Substrate: <input type="checkbox"/>
1.392	Index of Refraction (n_d):
60-40	Surface Quality:
97.29	Abbe Number (v_d):
Random	Axis Orientation:
150 - 6000	Wavelength Range (nm):
λ/2 @ 632.8nm	Surface Flatness (P-V):

Material Properties

2.64	Density (g/cm³):
37	Coefficient of Thermal Expansion CTE (10⁻⁶/°C):

Regulatory Compliance

View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details


- High Transmission from 150nm - 6µm
- Excellent Vacuum UV (VUV) Transmission
- Low Index of Refraction

Lithium Fluoride (LiF) Windows provide high, flat transmission from 150nm to 6µm. Lithium fluoride has excellent transmission in the vacuum ultraviolet (VUV) wavelength range of 150 - 200nm. Lithium fluoride also has a low index of refraction, allowing these windows to be used without an anti-reflection (AR) coating. Lithium Fluoride (LiF) Windows are ideal for use as UV transmission windows in spectroscopy applications, as a diffracting element in X-ray spectrometry, or as infrared windows for thermal imaging applications.

Note: Lithium fluoride is sensitive to thermal shock and is attacked by atmospheric moisture at temperatures above 400°C.

Technical Information

Lithium Fluoride (LiF)



Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools