

[See all 16 Products in Family](#)

TECHSPEC® 10mm Dia., 3mm Thick, 1 Side VIS-EXT Sapphire Window



Single-Side AR-Coated Sapphire Windows

Stock #90-058 **NEW** 20+ In Stock

- 1 + MRP ₹7,217

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-24	₹7,217 each
Qty 25-50	₹5,783 each
Qty 51-99	₹5,401 each
Need More?	Request Quote

Product Downloads

General

Protective Window **Type:**

Physical & Mechanical Properties

9 **Clear Aperture CA (mm):**

Diameter (mm):

10.00 ±0.05	Diameter Tolerance (mm):
±0.05	
	Thickness (mm):
3.00 ±0.05	
	Parallelism (arcmin):
≤3.5	
	Bevel:
Protective as needed	
	Clear Aperture (%):
90	
	Edges:
Fine Ground	
	Poisson's Ratio:
0.27	
	Young's Modulus (GPa):
435	
	Knoop Hardness (kg/mm²):
1,900.00	

Optical Properties

	Coating:
VIS-EXT (350-700nm)	
	Substrate: <input type="checkbox"/>
Sapphire (Al ₂ O ₃)	
	Index of Refraction (n_d):
1.77	
	Surface Quality:
80-50	
	Abbe Number (v_d):
72.24	
	Birefringence (n_o-n_e):
0.008 for Visible Light Orthogonal to Optical Axis	
	Axis Orientation:
Random	
	Coating Specification:
R _{avg} <0.5% @ 350 - 700nm	
	Wavelength Range (nm):
350 - 700	

Material Properties

	Density (g/cm³):
3.97	
	Coefficient of Thermal Expansion CTE (10⁻⁶/°C):
8.8	

Regulatory Compliance

	Certificate of Conformance:
View	
	Country of Origin:
Switzerland	
	Imported By:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

Product Details

- Combines the High Transmission of an AR-Coating with the Ruggedness of Sapphire
- Ideal for Applications Where High Environmental Resistance is Required
- Uncoated Surface can Withstand Intensive Cleaning and Abrasion

TECHSPEC® Single-Side AR-Coated Sapphire Windows feature a durable single-crystal sapphire substrate with an Anti-Reflection coating on one side for improved performance. The single-surface coating combines the benefits of higher transmission with the hardness, strength, and chemical resistance of sapphire. These windows are available in VIS-NIR (400-1000nm) or VIS-EXT (350-700nm) single-sided coating options. TECHSPEC® Single-Side AR-Coated Sapphire Windows can be used with the uncoated surface facing outwards to resist abrasion or harsh chemicals, ensuring the coated surface is not exposed to conditions that may cause damage and reduce performance. These windows are ideal for applications in food or healthcare where intensive cleaning is necessary.