

[See all 6 Products in Family](#)

10mm Dia., 5.1mm Thick, Uncoated, ISP Optics Silicon (Si) Hyper Hemispherical Lens | HRSI-HS-10-5.1

See More by [ISP Optics](#)



Stock **#24-725** CLEARANCE **3 In Stock**

-

1

+

₹46,367

ADD TO CART

Volume Pricing	
Qty 1+	₹46,367 each
Need More?	Request Quote

Product Downloads

General	
Half-Ball Lens	Type:
HRSI-HS-10-5.1	Model Number:

Physical & Mechanical Properties	
10.00 ±0.01	Diameter (mm):

5.10 ±0.05	Center Thickness CT (mm):
5.00	Radius R (mm):
Optical Properties	
Silicon (Si)	Substrate:
Uncoated	Coating:
1200 - 7000	Wavelength Range (nm):
3.422 @5µm	Index of Refraction (n _d):
60-40	Surface Quality:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:
Latvia	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- High Numerical Apertures
- Ideal for Fiber and LED Coupling
- Available with Fused Silica, Si, CaF₂, or ZnSe Substrates

ISP Optics Hemispherical (Half-Ball) Infrared (IR) Lenses are ideal for LED and fiber coupling of visible and infrared (IR) light sources. Hemispherical lenses are made by cutting a spherical (ball) lens in half, facilitating easier mounting compared to spherical (ball) lenses. These lenses are available with Fused Silica, Silicon, Calcium Fluoride, or Zinc Selenide substrates to provide coverage for applications from the ultraviolet to the long-wave infrared. ISP Optics Hemispherical (Half-Ball) Infrared (IR) Lenses feature high numerical apertures for applications including fiber coupling, microscopy, and IR laser measurement. The lenses with Silicon substrates are available as either standard hemispherical lenses or hyper-hemispherical lenses.

Note: Special care should be taken when handling Zinc Selenide as it is a toxic material. Always wear rubber or plastic gloves to avoid risk of contamination.

Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools