

TECHSPEC[®] 10mm Dia., Vacuum UV (VUV) Mirror



Precision Ultraviolet Mirrors

Stock **#18-726** 20+ In Stock

-

1

+

₹23,884

 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹23,884 each
Qty 6-25	₹19,016 each
Qty 26-49	₹17,822 each
Need More?	Request Quote

Product Downloads

General

Flat Mirror

Type:

Physical & Mechanical Properties

10.00 +0.0/-0.2

Diameter (mm):

Thickness (mm):

2.00 ±0.20	
Commercial Polish	Back Surface:
90	Clear Aperture (%):
<30	Parallelism (arcsec):
Optical Properties	
Metal	Coating Type:
Enhanced Aluminum (120-600nm)	Coating:
λ/10	Surface Flatness (P-V):
120 - 600	Wavelength Range (nm):
120	Design Wavelength DWL (nm):
Fused Silica (Corning 7980)	Substrate: □
0	Angle of Incidence (°):
Ravg ≥78% @ 120 - 125nm Ravg ≥85% @ 120 - 600nm	Coating Specification:
20-10	Surface Quality:

Material Properties	
10 ⁻⁷ Torr	Vacuum Compatibility:

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

• 120nm and 190nm Design Wavelengths


• Average Reflectivity >85% Across Specified Range



• Enhanced Metallic Coatings for Broadband Reflectivity through the Visible Region

TECHSPEC® Precision Ultraviolet Mirrors are ideal for most commercially available light sources and are offered in both Deep UV (DUV) and Vacuum UV (VUV) enhanced coating options. The DUV coating offers excellent reflection from 190nm to the long-wave infrared (LWIR), while the VUV coating has optimized reflection from 120nm to the LWIR. These mirrors are designed for 0° angle of incidence and feature an aluminum-based coating for low polarization sensitivity. TECHSPEC® Precision Ultraviolet Mirrors have an average reflectivity of greater than 85% across a specified range. The mirrors are available in diameters ranging from 5 to 50mm.

Note: The soft coating can be easily damaged by fingerprints and aerosols.

Technical Information





Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

Compatible Mounts