

[See all 9 Products in Family](#)

10mm Dia x 20mm Focal Length, Spherical Mirror



Stock **#46-232** **20+ In Stock**

- 1 + MRP ₹4,388

i Price inclusive of all taxes

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-49 | ₹4,388 each |
| Qty 50-99 | ₹3,935 each |
| Need More? | Request Quote |

Product Downloads

General

Spherical Mirror **Type:**

Physical & Mechanical Properties

10.00 +0.00/-0.30 **Diameter (mm):**

Ground **Back Surface:**

Center Thickness CT (mm):

3.00

Center Thickness Tolerance (mm):

±0.30

Edge Thickness ET (mm):

3.31

Edges:

Ground

Radius R (mm):

40.0

Optical Properties

Coating Type:

Metal

Coating:

Protected Aluminum (400-2000nm)

Wavelength Range (nm):

400 - 2000

Effective Focal Length EFL (mm):

20.00

Substrate:

[N-BK7](#)

Aperture (f/#):

f/2

Coating Specification:

R_{avg} >85% @400 - 700nm
R_{avg} >90% @400 - 2000nm

Focal Length Tolerance (%):

±2

Surface Accuracy:

λ/4

Surface Quality:

60-40

Radius of Curvature (mm):

40.00

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 247:

[Compliant](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Aluminum Coating
- Ideal for UV, Visible, and IR Applications
- Multiple Diameter and f/# Combinations Available

λ/4 Spherical Mirrors have flat rear surfaces and aluminum coated spherical front surfaces. These mirrors are ideal for applications in UV, VIS, and IR wavelength ranges.

Technical Information

