

[See all 36 Products in Family](#)

**TECHSPEC® 10mm Dia x 8mm FL, Uncoated Molded Aspheric Condenser Lens**



TECHSPEC Molded Aspheric Condenser Lenses

Stock **#36-164** **20+ In Stock**

[Other Coating Options](#)

1 MRP ₹2,246

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-10	₹2,246 each
Qty 11-49	₹2,018 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Condenser Lens **Type:**

**Note:**  
[Click here](#) for more information on the ISO 10110 surface quality specification.

**Physical & Mechanical Properties**

**Diameter (mm):**

10.00 +0.0/-0.2	
≤25	<b>Centering (arcmin):</b>
8.78	<b>Clear Aperture CA (mm):</b>
3.22	<b>Edge Thickness ET (mm):</b>
6.79 ±0.30	<b>Center Thickness CT (mm):</b>
Protective as needed	<b>Bevel:</b>
10.00	<b>Diameter of Asphere (mm):</b>
Plano	<b>Shape of Back Surface:</b>

## Optical Properties

8.00 @ 587.6nm	<b>Effective Focal Length EFL (mm):</b>
0.62	<b>Numerical Aperture NA:</b>
3.2	<b>Back Focal Length BFL (mm):</b>
<a href="#">Liba2000+</a>	<b>Substrate:</b> <input type="checkbox"/>
±5	<b>Focal Length Tolerance (%):</b>
Uncoated	<b>Coating:</b>
Molded Side: 5/3 x 0.4; E 0.2 Polished Side: 5/3 x 0.25; E 0.2	<b>Surface Quality:</b>
0.8	<b>f/#:</b>
58.9	<b>Abbe Number (v<sub>d</sub>):</b>
587.6	<b>Design Wavelength DWL (nm):</b>
1.52	<b>Index of Refraction (n<sub>d</sub>):</b>
∞	<b>Radius R<sub>2</sub> (mm):</b>
350 - 2000	<b>Wavelength Range (nm):</b>
Infinite	<b>Conjugate Distance:</b>
587.6	<b>Focal Length Specification Wavelength (nm):</b>

## Material Properties

9.4	<b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b>
-----	---

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">Compliant</a>	<b>Reach 223:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
Poland	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- High Numerical Apertures
- Fully Documented for OEM Integration
- Ideal for Illumination Applications

TECHSPEC® Molded Aspheric Condenser Lenses have been designed for integration into the illumination path of OEM instrumentation. Available in 5 to 50mm diameters, the small diameter lenses are ideal for medical devices or portable instruments, while the larger lenses are typically integrated into benchtop analytical equipment including biotech instruments such as DNA sequencers and polymerase chain reaction (PCR) testing platforms. The front aspheric surface is molded to eliminate spherical aberrations, while the second surface is ground and polished for improved performance. Full prescription data and drawings are available to aid in design integration.

**Note:** For custom coating options, please [contact us](#).

## Compatible Mounts

;