

**TECHSPEC® 10mm Inner Single Optic Mount**



TECHSPEC Multi-Element Inner Single Optic Mounts

Stock #38-748 **20+ In Stock**

1 MRP ₹4,137

● Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-4	₹4,137 each
Qty 5+	₹3,703 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Fixed **Type:**  
Optic Mount (Fixed) **Function:**

**Physical & Mechanical Properties**

9.0 **Total Length (mm):**

Min. Thickness of Compatible Optics (mm):  
1.0

Max. Thickness of Compatible Optics (mm):  
4.0

Clear Aperture CA (mm):  
9.0

Construction:  
Matte Black Anodized Aluminum (6061-T6)

Edge Thickness of Compatible Optics (mm):  
4.0

## Threading & Mounting

Thread Type:  
M29 x 0.75

Diameter of Compatible Optics (mm):  
10.0

## Regulatory Compliance

RoHS 2015:  
[Compliant](#)

Certificate of Conformance:  
[View](#)

Reach 250:  
[Compliant](#)

Country of Origin:  
China

Imported By:  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Mounts for a Variety of Optical Component Diameters and Thicknesses
- M29 Outer Diameter Threads Allow Easy Positioning Within [Outer Tubes](#)
- One Retainer Ring and One Delrin Ring are Included
- Click [Here](#) to See How to Use the Multi-Element Tube System Components to Build an Optical System.

TECHSPEC® Multi-Element Inner Single Optic Mounts are designed to mount a variety of optical components. The mounts support optical diameters from 5mm to 25.4mm, and edge thicknesses of 4mm to 17mm. With M29 x 0.75 outer diameter threads, these mounts can be easily positioned along the optical axis of our TECHSPEC® Multi-Element Outer Tubes. TECHSPEC® Multi-Element Inner Single Optic Mounts include one Delrin ring to ensure secure clamping force between the retainer ring and optic without damaging the optic.

**Note:** Our specially designed ME Spanner Wrench ([#13-567](#)) is highly recommended to move Inner Single Optic Mounts back and forth smoothly utilizing a combined metric and English graduated scale. The hollow design enables transmission of output beam while adjusting lens position. Non-scaled ME Spanner Wrench ([#11-046](#)) is also available.