

# 11 x 11mm, 800nm, Corning Polarcor™ Glass Polarizer



Corning Polarcor™ Glass Polarizers

Stock **#13-615** **3 In Stock**

MRP ₹70,119

**Price inclusive of all taxes**

**ADD TO CART**

### Volume Pricing

Qty 1+	₹70,119 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### Physical & Mechanical Properties

Length (mm):  
11.00

Dimensions (mm):  
11.0 x 11.0

Thickness (mm):  
0.50 ±0.05

Dimensional Tolerance (mm):  
±0.1

Width (mm):

11.00

**Knoop Hardness (kg/mm<sup>2</sup>):**

480.00

**Young's Modulus (GPa):**

58.605

**Poisson's Ratio:**

0.21

## Optical Properties

**Angle of Incidence (°):**

0 ±5

**Coating:**

BBAR (740-860nm)

**Design Wavelength DWL (nm):**

800

**Extinction Ratio:**

>10,000:1

**Substrate:**

Borosilicate Glass Containing Elongated Silver Crystals

**Minimum Transmission (%):**

>91.3

**Surface Quality:**

40-20

**Coating Specification:**

R<sub>avg</sub> <0.4% @ 740 - 860nm

**Wavelength Range (nm):**

740 - 860

**Index of Refraction (n<sub>d</sub>):**

1.5161

**Abbe Number (v<sub>d</sub>):**

57.6

## Hardware & Interface Connectivity

**Insertion Loss (dB):**

<0.39

## Material Properties

**Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):**

6.5

**Density (g/cm<sup>3</sup>):**

2.412

## Regulatory Compliance

**RoHS 2015:**

Compliant

**Reach 224:**

Compliant

**Certificate of Conformance:**

[View](#)

**Country of Origin:**

United States

**Imported By:**

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- High Extinction Ratio and Low Insertion Loss in the NIR
- Resistant to Chemical, Physical, and Thermal Damage

- Suitable for High Power Applications
- Range of Standard Sizes and Custom Options Available

Coming Polarcor™ Glass Polarizers feature a high extinction ratio and low insertion loss at wavelengths in the NIR. These linear polarizers consist of elongated silver crystals aligned within a borosilicate glass substrate, providing a polarization mechanism based on resonant absorption. This polarization mechanism causes light of unwanted polarization directions to be absorbed, ensuring that stray light is eliminated. Coming Polarcor™ Glass Polarizers can be used to polarize light, block polarized light, reduce reflections, improve image contrast, modulate and control the intensity of light, or improve the signal to noise ratio. These polarizers are ideal for integration into polarization-dependent optical isolators, optical modulators, and other polarization-based devices in the telecommunications, medical, and defense industries.

---