

[See all 10 Products in Family](#)

TECHSPEC® 1:1.43 with 35mm and 50mm EFL Achromats, NIR Achromatic Pair



TECHSPEC Mounted Near-IR (NIR) Achromatic Lens Pairs

Stock #47-294 [CONTACT US](#)

⊖ 1 ⊕ MRP ₹27,644

● Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹27,644 each
Qty 6-25	₹22,096 each
Qty 26-49	₹21,389 each
Need More?	Request Quote

Product Downloads

General

Relay Lens **Type:**

Physical & Mechanical Properties

22.0 **Clear Aperture CA (mm):**

Center Air Spacing (mm):

Housing Diameter (mm):

30.0 +0.0/-0.10

Housing Length (mm):

34.00 ±0.2

Image Distance (mm):

39.72

Construction:

Achromat Pair in Anodized Aluminum Housing

Optical Properties

Substrate:

[N-LAK22 / N-SF6 / N-LAK22 / N-SF6](#)

Surface Quality:

40-20

Working f#:

f/2.24

Coating:

NIR II (750-1550nm)

Coating Specification:

$R_{\text{abs}} \leq 1.5\%$ @ 750 - 800nm

$R_{\text{abs}} \leq 1.0\%$ @ 800 - 1550nm

$R_{\text{avg}} \leq 0.7\%$ @ 750 - 1550nm

Effective Focal Length EFL A (mm):

35.00

Effective Focal Length EFL B (mm):

50.00

Magnification:

1:1.43

Object Distance (mm):

25.00

Wavelength Range (nm):

750 - 1550

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- 30mm Diameter Package Designed for NIR Applications
- Optimized for Various Magnification Ratios
- Ideal for Integration into OEM Applications
- NIR II Coated for 750-1550nm

Our 15.0mm and 30.0mm Mounted Achromatic Pairs combine our popular TECHSPEC® achromats into common configurations used for relay and projection applications. Packaged in a slim-line aluminum housing, each pair is ready for integration into a host of OEM applications, eliminating the need to handle loose optics. Each lens has also been oriented for optimum system performance. All lenses AR coated. Lower f# pairs may not be ideal for imaging applications depending on the performance requirements. Cylinder lenses can be incorporated into empty barrels in order to generate lines or sheets of light.

Technical Information

