


[See all 4 Products in Family](#)

## 11" x 11", 0.085" FL, Lenticular Array



Stock **#43-028** **7 In Stock**

⊖ 1 ⊕ ₹10,276

**ADD TO CART**

Volume Pricing	
Qty 1-10	₹10,276 each
Qty 11-49	₹9,264 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Lens Array **Type:**

64 per 25.4mm **Number of Lenses:**

#### Physical & Mechanical Properties

0.09 **Center Thickness CT (inches):**

2.20 **Center Thickness CT (mm):**

±0.05 **Dimensional Tolerance (inches):**

11 x 11 **Dimensions (inches):**

279.4 x 279.4 **Dimensions (mm):**

11 x 11 **Effective Size (inches):**

±40 **Thickness Tolerance (%):**

±0.88 **Thickness Tolerance (mm):**

## Optical Properties

2.16 **Effective Focal Length EFL (mm):**

Acrylic **Substrate:**

Uncoated **Coating:**

400 - 1100 **Wavelength Range (nm):**

0.09 **Effective Focal Length EFL (inches):**

1.49 **Index of Refraction (n<sub>d</sub>):**

## Environmental & Durability Factors

80 (Maximum) **Operating Temperature (°C):**

## Regulatory Compliance

**RoHS 2015:**  
Compliant

**Certificate of Conformance:**  
View

**Reach 242:**  
Compliant

United States **Country of Origin:**

Edmund Optics India Private Limited **Imported By:**

## Product Details

- Arrays of Conventional Cylinder Lenses
- Used as High-Efficiency Diffusers
- Cylindrical Axis of Lenslet is Aligned Along the First Dimension

Lenticular Arrays consist of an array of conventional cylindrical lenses which efficiently divide, focus, and diffuse light rays. The focal length of each cylindrical lenslet is typically 3 to 5 times its width and its axis is aligned along the first dimension specified under array dimensions. Lenticular Arrays are ideal for use as high-efficiency diffusers within short working distances, projection screens and stereoscopic (3D) photography.

## Technical Information

