

# 12", Blue 470nm, UltraSeal Washdown Bar Light

See More by [Advanced Illumination](#)



Advanced Illumination UltraSeal Washdown Bar Lights

Stock **#90-802** NEW **1 In Stock**

-

1

+

₹1,23,540

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | ₹1,23,540 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

## SPECIFICATIONS

| General               |                       |
|-----------------------|-----------------------|
| AL247M12-470ICSS      | Model Number:         |
| 50000                 | LED Lifetime (hours): |
| Type of Illumination: |                       |

|                                                                                                                                                                                                                                                       |                             |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------|
| LED Illuminator                                                                                                                                                                                                                                       |                             |
| <div>Note:<br/>Optional Manual Intensity Adjustment <a href="#">#86-887</a> and <a href="#">#89-555</a> are Available</div>                                                                                                                           |                             |
| Advanced Illumination                                                                                                                                                                                                                                 | Manufacturer:               |
| Bar Light                                                                                                                                                                                                                                             | Geometry:                   |
| Constant                                                                                                                                                                                                                                              | Illumination Mode:          |
| Physical & Mechanical Properties                                                                                                                                                                                                                      |                             |
| 323.8 x 42.9 x 24                                                                                                                                                                                                                                     | Dimensions (mm):            |
| 657                                                                                                                                                                                                                                                   | Weight (g):                 |
| Optical Properties                                                                                                                                                                                                                                    |                             |
| Blue                                                                                                                                                                                                                                                  | Color:                      |
| 470                                                                                                                                                                                                                                                   | Wavelength (nm):            |
| Electrical                                                                                                                                                                                                                                            |                             |
| 0.70A                                                                                                                                                                                                                                                 | Minimum Input Current:      |
| Hardware & Interface Connectivity                                                                                                                                                                                                                     |                             |
| Flying Leads                                                                                                                                                                                                                                          | Connector:                  |
| 24V                                                                                                                                                                                                                                                   | Input Voltage (V):          |
| <div>Power Supply:<br/>Power Supply Required and Sold Separately.<br/>USA: <a href="#">#66-855</a><br/>Europe: <a href="#">#66-855</a><br/>Japan: <a href="#">#89-513</a><br/>Korea: <a href="#">#33-773</a><br/>China: <a href="#">#66-855</a></div> |                             |
| Environmental & Durability Factors                                                                                                                                                                                                                    |                             |
| 0 - 60                                                                                                                                                                                                                                                | Operating Temperature (°C): |
| IP69K                                                                                                                                                                                                                                                 | Environmental Rating:       |
| Regulatory Compliance                                                                                                                                                                                                                                 |                             |
| <a href="#">View</a>                                                                                                                                                                                                                                  | Certificate of Conformance: |

## PRODUCT DETAILS

- IP69K Certified for Extreme Washdown Environments
  - Stainless Steel Housing
  - High Intensity Output up to 70,200 Lux
  - Optional Manual Intensity Adjustments ([#86-887](#) and [#89-555](#)) Recommended
- Advanced Illumination UltraSeal Washdown Bar Lights offer intense, direct illumination up to 70,200 Lux while providing maximum protection in extreme environmental conditions. These IP69K certified Bar Lights were designed with a crevice-free design to withstand high temperature wash-down procedures and material buildup. The 316 stainless steel is FDA compliant, making them a suitable option for food or pharmaceutical inspection environments. Advanced Illumination UltraSeal Washdown Bar Lights are ideal for hygienic and aseptic manufacturing applications, such as prolonged liquid immersion and high-pressure steam cleaning common in food and beverage inspection and processing.
- Note:** Requires 24V power supply [#66-855](#). Manual Intensity Adjustment [#86-887](#) and [#89-555](#) are recommended and sold separately.