

[See all 33 Products in Family](#)

12 x 12mm, 500µm Pitch, 6° Div., Double Cyl. Lens Array VIS-NIR



Stock #72-595 **1 In Stock**

- 1 + MRP ₹99,449

● Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-10	₹99,449 each
Qty 11-25	₹79,846 each
Qty 26-49	₹74,587 each
Need More?	Request Quote

Product Downloads

General

Lens Array **Type:**

Physical & Mechanical Properties

12.0 x 12.0 ±0.10 **Dimensions (mm):**

2.150 **Radius R (mm):**

2.00 ±0.10 **Thickness (mm):**

Optical Properties

Effective Focal Length EFL (mm):
4.78 @ 1064nm

Substrate:
[Fused Silica](#) (Corning 7980)

Coating:
VIS-NIR (400-1000nm)

Wavelength Range (nm):
400 - 1000

Coating Specification:
R_{abs} ≤ 0.25% @ 880nm @ 0° AOI
R_{avg} ≤ 1.25% @ 400 - 870nm @ 0° AOI
R_{avg} ≤ 1.25% @ 890 - 1000nm @ 0° AOI

Divergence Angle (°):
6.0 (Full Width)

Pitch (µm):
500.00

Array Type:
Double-Sided (with cross-oriented lenses)

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 250:
[Compliant](#)

Country of Origin:
Switzerland

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Generate Non-Gaussian Line Patterns
- Ideal for Light Homogenization
- Excellent Performance from 193nm – 2.5µm

Cylindrical Microlens Arrays are used to homogenize a variety of light sources, including lasers or high power LEDs. Unlike [Square Microlens Arrays](#), which generate spot patterns, Cylindrical Microlens Arrays yield non-gaussian line patterns, and are ideal for welding, drilling, or laser ablation applications from the UV to IR. Cylindrical Microlens Arrays are available uncoated, VIS-NIR, or UV-NIR coated, including options with lenses on a single side for line generation applications or double-sided (with cross-oriented lenses) for beam homogenisation. Additionally, these lenses can be used as fast axis collimators.

Coating Curves