

TECHSPEC<sup>®</sup> 12.7mm Dia. 515nm 0-45°, Yb:YAG Laser Line Mirror



TECHSPEC<sup>®</sup> Yb:YAG Laser Line Mirrors

Stock **#38-880** 7 In Stock

-

1

+

₹11,444

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹11,444 each                  |
| Qty 6-25       | ₹10,354 each                  |
| Qty 26-49      | ₹9,108 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                          |                       |
|----------------------------------|-----------------------|
| Laser Mrror                      | Type:                 |
| Physical & Mechanical Properties |                       |
| <3                               | Parallelism (arcmin): |
| 90                               | Clear Aperture (%):   |

|                                             |                                |
|---------------------------------------------|--------------------------------|
| Commercial Polish                           | Back Surface:                  |
|                                             |                                |
| 12.70 +0.00/-0.10                           | Diameter (mm):                 |
|                                             |                                |
|                                             |                                |
| 6.35 ±0.2                                   | Thickness (mm):                |
|                                             |                                |
| Optical Properties                          |                                |
| 10-5                                        | Surface Quality:               |
|                                             |                                |
| 99.8                                        | Reflection at DWL (%):         |
|                                             |                                |
|                                             |                                |
| R <sub>abs</sub> ≥99.8% @ 515nm             | Coating Specification:         |
|                                             |                                |
| 509 - 520                                   | Wavelength Range (nm):         |
|                                             |                                |
|                                             |                                |
| λ/10                                        | Surface Flatness (P-V):        |
|                                             |                                |
| Dielectric                                  | Coating Type:                  |
|                                             |                                |
|                                             |                                |
| Laser Mirror (515nm)                        | Coating:                       |
|                                             |                                |
| 515                                         | Design Wavelength DWL (nm):    |
|                                             |                                |
|                                             |                                |
| 0-45                                        | Angle of Incidence (°):        |
|                                             |                                |
| <a href="#">Fused Silica</a> (Corning 7980) | Substrate: □                   |
|                                             |                                |
|                                             |                                |
| 10 J/cm <sup>2</sup> @ 515nm, 20ns, 20Hz    | Damage Threshold, By Design: □ |
|                                             |                                |
|                                             |                                |
| Regulatory Compliance                       |                                |
| <a href="#">Compliant</a>                   | RoHS 2015:                     |
|                                             |                                |
| <a href="#">View</a>                        | Certificate of Conformance:    |
|                                             |                                |
|                                             |                                |
| <a href="#">Compliant</a>                   | Reach 250:                     |
|                                             |                                |
|                                             |                                |
| United States                               | Country of Origin:             |
|                                             |                                |
| Edmund Optics India Private Limited         | Imported By:                   |
|                                             |                                |

## Product Details

- >99.8% Reflectivity at Yb:YAG Harmonic Frequencies
- Guaranteed High Laser Damage Thresholds
- 10-5 Surface Quality for Reduced Scatter in Laser Applications
- [TECHSPEC® Laser Mirror Substrates](#) and [TECHSPEC® Nd:YAG Laser Line Mirrors](#) Also Available

TECHSPEC® Yb:YAG Laser Line Mirrors are designed to meet the demanding requirements of Ytterbium doped fiber (Yb:doped fiber) and thin-disk laser systems. These mirrors feature laser grade substrates with λ/10 surface flatness and 10-5 surface quality to minimize scattering effects. The durable dielectric coatings are designed for high reflectivity at their design wavelengths as well as high damage thresholds at both continuous wave and pulsed laser operating conditions. TECHSPEC Yb:YAG Laser Line Mirrors are ideal for laser applications that include laser ablation, welding, drilling, cutting, and sintering. Dielectric Yb:YAG mirror coatings for applications which require 343nm, 515nm, and 1030nm are available.

**Note:** Contact us for customizable wavelengths, sizes, and varying AOI versions.

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts