

120 MHz Fiber Coupled Optical Receiver Module



Stock #87-324 CLEARANCE 5 In Stock

MRP ₹19,859

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹19,859 each
Need More?	Request Quote

Product Downloads

Optical Properties

1310 - 1550 **Wavelength Range (nm):**

50/125/245/900 **Fiber Diameter (µm):**

Sensor

25.00 **Dynamic Range (dB):**

Electrical

Hardware & Interface Connectivity

FC/PC Connector:

Regulatory Compliance

View Certificate of Conformance:

Country of Origin: United States


Imported By:
 Edmund Optics India Private Limited
 267, Greystone Building, Second Floor,
 6th Cross Rd, Binnamangala,
 Stage 1, Indiranagar, Bengaluru,
 Karnataka, India 560038
 Phone: +91- 80-6845 0000

Product Details

- High Sensitivity and Overload Power with Wide Dynamic Range
- Designed for Bandwidths of 3MHz and 120MHz and Wavelength Ranges of 1310 – 1550nm
- Ideal for Biomedical, Industrial, or Telecommunication Optical Sensor Systems

Fiber-Coupled Optical Receiver Modules are ideal for use in biomedical optical sensor systems or for industrial and telecommunication sensing applications. Fiber-Coupled Optical Receiver Modules feature high sensitivity and high overload power, in addition to wide dynamic ranges. These receiver modules are designed for use in common telecommunication wavelength ranges.

Technical Information



Pin	Function
1	-5V detector bias
2, 6, 9, 11	No connection
12, 13, 14	No connection
3, 5, 8	Ground
4	-5V (LDFR = NC)
7	Output
10	+5V