

[See all 20 Products in Family](#)

## 1200 Grooves, 30mm Square, 750nm NIR Ruled Grating



Stock #55-261 **3 In Stock**

- 1 + MRP ₹22,701

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-9	₹22,701 each
Qty 10-24	₹20,431 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Reflective Diffraction Grating **Type:**

### Physical & Mechanical Properties

30.0 x 30.0 ±0.5 **Dimensions (mm):**

90 **Clear Aperture (%):**

**Construction:**

Ruled Grating

**Direction of Grooves:**

Parallel to Short Dimension

**Length (mm):**

30.00

**Thickness (mm):**

9.50 ±0.5

**Width (mm):**

30.00

**Alignment of Grooves to Edge (°):**

±0.5

### Optical Properties

**Groove Density (grooves/mm):**

1200

**Wavelength Range (nm):**

700 - 3000

**Blaze Wavelength (nm):**

750

**Blaze Angle (°):**

26.73

**Coating:**

Bare Gold

**Substrate:**

Float Glass

### Regulatory Compliance

**RoHS 2015:**

[Compliant](#)

**Certificate of Conformance:**

[View](#)

**Reach 247:**

[Compliant](#)

**Country of Origin:**

United States

**Imported By:**

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000


## Product Details

- Increased Reflection from 700 - 1100nm


Near-IR (NIR) Reflective Gold Gratings are ruled gold-coated versions of our commercial gratings. These gratings provide increased reflection from 700 - 1100nm. This makes them an excellent choice for applications such as fiber optic pulse compression and spectroscopy setups using [silicon detectors](#). Near-IR (NIR) Reflective Gold Gratings feature a float glass substrate and a ruled grating construction. The gratings are available in three sizes, with varying groove densities and blaze wavelengths.

**Handling Gratings:** Gratings require special handling, making them prone to fingerprints and aerosols. Gratings should only be handled by the edges. Before attempting to clean a grating, please [contact us](#).

## Technical Information



### Typical Efficiency Curves for Ruled Gratings Optimized (Blaze) Wavelengths from 250-400nm



## Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools