

**TECHSPEC® 12.5 x 17.5mm Protected Gold,  $\lambda/4$  Mirror**



Stock #25-748 **2 In Stock**

⊖ 1 ⊕ MRP ₹9,029

● Price inclusive of all taxes

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹9,029 each                   |
| Qty 6-25       | ₹7,264 each                   |
| Qty 26-49      | ₹6,760 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

**General**

Flat Mirror **Type:**

**Physical & Mechanical Properties**

3.00 ±0.25 **Thickness (mm):**

12.5 x 17.5 **Dimensions (mm):**

|                      |                                    |
|----------------------|------------------------------------|
| Commercial Polish    | <b>Back Surface:</b>               |
| Protective as needed | <b>Bevel:</b>                      |
| 90                   | <b>Clear Aperture (%):</b>         |
| +0.0/-0.25           | <b>Dimensional Tolerance (mm):</b> |
| Fine Ground          | <b>Edges:</b>                      |
| 12.50                | <b>Length (mm):</b>                |
| 17.50                | <b>Width (mm):</b>                 |

## Optical Properties

|   |  |
|---|--|
| 0.7 - 10  | <b>Wavelength Range (µm):</b>                                |
| Metal   | <b>Coating Type:</b>   |
| Protected Gold (700-10000nm)  | <b>Coating:</b>  |
| λ/4   | <b>Surface Flatness (P-V):</b>                               |
| 700 - 10000   | <b>Wavelength Range (nm):</b>                                |
| <b>BOROFLOAT®</b>   | <b>Substrate:</b> <input type="checkbox"/>                   |
| R <sub>avg</sub> >96% @ 700 - 2000nm<br>R <sub>avg</sub> >96% @ 2000 - 10,000nm | <b>Coating Specification:</b>                                |
| 60-40   | <b>Surface Quality:</b>                                      |
| 0.8 J/cm <sup>2</sup> @ 1064nm, 10ns  | <b>Damage Threshold, Reference:</b> <input type="checkbox"/> |

## Regulatory Compliance

|   |                                    |
|---|------------------------------------|
| <b>Compliant</b>  | <b>RoHS 2015:</b>                  |
| <b>View</b>   | <b>Certificate of Conformance:</b> |
| <b>Compliant</b>  | <b>Reach 247:</b>                  |
| United States   | <b>Country of Origin:</b>          |
| Edmund Optics India Private Limited<br>267, Greystone Building, Second Floor,<br>6th Cross Rd, Binnamangala,<br>Stage 1, Indiranagar, Bengaluru,<br>Karnataka, India 560038<br>Phone: +91- 80-6845 0000 | <b>Imported By:</b>                |

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Available in a Wide Range of Sizes and Shapes
- Precision Metallic Mirror Coatings
- [Contact Us](#) for Custom Sizes

TECHSPEC® λ/4 First Surface Mirrors feature a high reflectivity coating deposited on the front surface of the glass substrate. The coated surface should be oriented to reflect incident light. TECHSPEC λ/4 First Surface Mirrors are offered in circular, square, and rectangular dimensions. First surface mirrors are ideal for applications requiring the mirror to be mounted at 45° in order to produce a 90° bend in the light path. These first surface mirrors easily mount into a [range of optical mounts](#) to facilitate application integration. The mirrors have available coatings of enhanced aluminum, protected aluminum, protected silver, and protected gold.

**Note:** Surface flatness is measured before coating.

A range of mounts specifically compatible with individual TECHSPEC® First Surface Mirrors can be found on product web pages.

