

**TECHSPEC®**

# 12.5 x 25mm, 0.33 Numerical Aperture, Uncoated, Truncated Precision Aspheric Lens



Stock #17-313 CLEARANCE **10 In Stock**

MRP ₹37,229

! Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹37,229 each
Qty 6-25	₹29,763 each
Qty 26-49	₹28,047 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Aspheric Lens Type:

**Physical & Mechanical Properties**

12.50 x 25.00 Dimensions (mm):

Centering (arcmin):

10.50 x23.00	<b>Clear Aperture CA (mm):</b>
5.49	<b>Edge Thickness ET (mm):</b>
9.72 ±0.10	<b>Center Thickness CT (mm):</b>
Protective as needed	<b>Bevel:</b>
Plano	<b>Shape of Back Surface:</b>

### Optical Properties

37.50 @587.6nm	<b>Effective Focal Length EFL (mm):</b>
0.33	<b>Numerical Aperture NA:</b>
31.09	<b>Back Focal Length BFL (mm):</b>
<a href="#">N-BK7</a>	<b>Substrate:</b> <input type="checkbox"/>
0.4λ	<b>Asphere Figure Error, RMS @ 632.8nm:</b>
Uncoated	<b>Coating:</b>
40-20	<b>Surface Quality:</b>
1.50	<b>f#:</b>
350 - 2200	<b>Wavelength Range (nm):</b>
Infinite	<b>Conjugate Distance:</b>
26.67	<b>Power (diopters):</b>

### Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
Singapore	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Rectangular and Square Aspheres in 5 x 5mm to 12.5 x 25mm sizes
- Precision Grade Aspheric Figure Error
- Ideal for Integration into Space Sensitive Laser Systems

TECHSPEC® Truncated Precision Aspheric Lenses are truncated versions of our [TECHSPEC Precision Aspheric Lenses](#). These aspheric lenses are CNC polished to achieve a 0.4λ (Waves) RMS aspheric figure error and then cut to square or rectangular sizes. The precision aspheric figure error of these lenses makes them advantageous for demanding imaging or laser systems requiring spherical aberration correction. TECHSPEC Truncated Precision Aspheric Lenses with their space saving form factors are ideal for integration into medical devices, life science instrumentation, and industrial laser systems. Please contact us if your application requires a [TECHSPEC Aspheric Lens](#) truncated to meet specific size requirements.

## Technical Information

