

[See all 8 Products in Family](#)

# 317.5mm/12.5" Optic Dia., Optical Cell Kinematic Mount



Stock **#36-480** [CONTACT US](#)

- 1 +

₹3,64,916

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | ₹3,64,916 each                |
| Qty 5-9        | ₹3,21,830 each                |
| Qty 10-25      | ₹2,96,129 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General               |                 |
|-----------------------|-----------------|
| Adjustable - Tip-Tilt | Type:           |
| Circular              | Type of Optics: |
| 7°                    | Range:          |

|                                          |                                           |
|------------------------------------------|-------------------------------------------|
| 12.56                                    | Inner Diameter (inches):                  |
| Three Spring-Loaded Clips                | Optic Holding Style:                      |
| Physical & Mechanical Properties         |                                           |
| 12.08                                    | Clear Aperture CA (inches):               |
| 306.8                                    | Clear Aperture CA (mm):                   |
| 203.2                                    | Optical Centerline (mm):                  |
| 16.00 x 8.00 x 15.00                     | Dimensions (inches):                      |
| 406.4 x 203.2 x 381.0                    | Dimensions (mm):                          |
| 41.0                                     | Weight (lbs):                             |
| Black Anodized Aluminum, Stainless Steel | Construction:                             |
| 12.50                                    | Diameter of Compatible Optics (inches):   |
| 8.00                                     | Optical Centerline (inches):              |
| 53.0                                     | Max. Thickness of Compatible Optics (mm): |
| 0.031                                    | Adjustment Screw Pitch (inches):          |
| Threading & Mounting                     |                                           |
| 317.5                                    | Size of Compatible Optics (mm):           |
| Regulatory Compliance                    |                                           |
| Compliant                                | RoHS 2015:                                |
| View                                     | Certificate of Conformance:               |
| United States                            | Country of Origin:                        |
| Edmund Optics India Private Limited      | Imported By:                              |

## Product Details

- Robust Kinematic Mounts for Larger Diameter Optics
- Ball Pivot and Fine Pitch Screws Provide Pitch and Roll
- 50% Greater Resolution than Micrometer Adjustments

Optical Cell Kinematic Mounts provide highly stable kinematic movement with two axis tilt (pitch and roll) provided by a precise ball pivot adjustment and an orthogonal three-point suspension. Adjustment is made by three 64-pitch screws (two 64-pitch screws for 1-2" diameter model). For the 6" diameter model, adjustment is made by two 64-pitch screws for and with three 32-pitch screws for 8" up to 12.5" diameter models. Optical Cell Kinematic Mounts feature fine pitch screws, which permit 50% greater resolution than a micrometer. An angled base on the mount allows for stand-alone installation and mounting. These mounts have integral optic cell design allowing optics to be held undistorted.

**Note:** For mounting 12" diameter optics in our 12.5" Diameter Optical Mount, use the 12.5" to 12" Adapter Kit (#12-226). The Adapter Kit and 12.5" Diameter Optical Mount are offered together as #12-227.

## Technical Information

| Optic Diameter | A            | B    | C    | D    | E    | F    | G    | H    | I | J    | K | Stock No.               |
|----------------|--------------|------|------|------|------|------|------|------|---|------|---|-------------------------|
| 1-2"           | 2.25-20 TPI  | 3.75 | 2.00 | 2.00 | 0.38 | 2.00 | 3.50 | 0.28 | - | 2.12 | - | <a href="#">#53-964</a> |
| 3"             | 3.25-20 TPI  | 5.75 | 3.00 | 4.00 | 1.25 | 3.38 | 6.25 | 0.28 | - | 5.00 | - | <a href="#">#53-965</a> |
| 4.25"          | 4.625-20 TPI | 5.75 | 3.00 | 4.00 | 1.25 | 3.38 | 6.25 | 0.28 | - | 5.00 | - | <a href="#">#57-872</a> |

1" - 4.25" Angled Optical Cell Mounts



Units: inches


4.25" Straight Optical Cell Mount



Units: inches

| Optic Diameter | A            | B     | C    | D     | E    | F    | G     | H    | I     | J     | K    | Stock No.               |
|----------------|--------------|-------|------|-------|------|------|-------|------|-------|-------|------|-------------------------|
| 6"             | 6.187-32 TPI | 8.00  | 6.00 | 5.00  | 5.00 | 4.50 | 8.00  | 0.28 | 5.75  | 6.00  | 1.19 | <a href="#">#36-474</a> |
| 8"             | 8.06         | 12.00 | 7.00 | 10.00 | 6.00 | 6.25 | 11.50 | 0.28 | 7.62  | 9.00  | 1.60 | <a href="#">#36-476</a> |
| 10"            | 10.06        | 16.00 | 8.00 | 12.00 | 6.00 | 8.00 | 15.00 | 0.53 | 9.58  | 12.50 | 1.75 | <a href="#">#36-478</a> |
| 12.5"          | 12.56        | 16.00 | 8.00 | 12.00 | 6.00 | 8.00 | 15.00 | 0.53 | 12.08 | 12.50 | 2.13 | <a href="#">#36-480</a> |

8" - 12.5" Angled Optical Cell Mounts



Units: inches