

12.5/12.7mm 12 Position Motorized Filter Wheel



#88-171 with cover



Stock **#88-398** [CONTACT US](#)

- 1 + MRP ₹2,22,463

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹2,22,463 each
Need More?	Request Quote

Product Downloads

General

Adjustable - Rotary **Type:**

Circular **Type of Optics:**

12 **Number of Filters:**

Filter Holder Response Time (seconds):

Adjacent Locations: 0.8

Yes **Motorized:**

Physical & Mechanical Properties

±0.25 **Repeatability (°):**

139.0 x 55.0 x 111.0 **Housing Dimension:**

7.0 **Max. Thickness of Compatible Optics (mm):**

Hardware & Interface Connectivity

USB Female Micro A **Connector:**

+5 VDC, 1.2 A **Power Requirement:**

Threading & Mounting

12.5 - 12.7 **Size of Compatible Optics (mm):**

M6 x 1.0, 1/4-20, M4 x 0.7, 8-32 **Compatible Post:**

Environmental & Durability Factors

0 to 60 **Operating Temperature (°C):**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **REACH 241:**

United States **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000


Product Details

- Manual or Automated Multi-Directional Control
- Interchangeable Filter Retaining Wheels
- Lightweight Design with Multiple Mounting Options

Miniature Motorized Filter Wheels are ideal for space constrained applications that require spectral selection, such as fluorescence microscopy, color CCD photography, or photometry. These stepper motor driven, optical encoder regulated filter wheels are designed to repeatedly select absolute positions either manually using a push button or remotely through an RS-232 or USB 2.0 interface. Miniature Motorized Filter Wheels feature two aperture positions, at 12:00 and 9:00, and a digital display which shows the current filter position. The six position filter wheel accepts 25mm filters, while the twelve position filter wheel accepts 12.5mm filters. The base of the unit features six threaded mounting holes to ease system integration, including one 1/4"-20, two #8-32, one M6, and two M4

Note: Accessories are available to increase or decrease compatible filter size.

Technical Information



#88-398

Quantity	Description
1	12.5mm Filter Wheel
1	12 Position Filter Retaining Wheel
1	5VDC Converter
1	USB 2.0A to USB Micro A (6ft cable)
1	RS-232 to RS-232 (6ft cable)

1	Software Flash Drive
2	Threaded Aperture Caps
6	Threaded 1/2" Filter Retaining Rings
1	5/64" Ball Driver
1	Operating Manual

#88-171

Quantity	Description
1	25mm Filter Wheel
1	6 Position Filter Retaining Wheel
1	5VDC Converter
1	USB 2.0A to USB Micro A (6ft cable)
1	RS-232 to RS-232 (6ft cable)
1	Software Flash Drive
2	Threaded Aperture Caps
6	Threaded 1" Filter Retaining Rings
1	5/64" Ball Driver
1	Operating Manual