

[See all 32 Products in Family](#)

TECHSPEC® 12.5mm Dia. x 3mm 532/1064nm, Dual Band Laser Mirror



Stock #20-371 **14 In Stock**

MRP ₹15,941

i Price inclusive of all taxes

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-5 | ₹15,941 each |
| Qty 6-25 | ₹13,923 each |
| Qty 26+ | ₹13,550 each |
| Need More? | Request Quote |

Product Downloads

General

Laser Mirror **Type:**

Physical & Mechanical Properties

<3 **Parallelism (arcmin):**

>90 **Clear Aperture (%):**

| | |
|---|--|
| Commercial Polish | Back Surface: |
| 12.50 +0.0/-0.2 | Diameter (mm): |
| 3.00 ±0.2 | Thickness (mm): |
| Optical Properties | |
| 10-5 | Surface Quality: |
| 99.5 | Reflection at DWL (%): |
| R _{abs} >99.5% @ 532 & 1064nm | Coating Specification: |
| M10 | Surface Flatness (P-V): |
| Dielectric | Coating Type: |
| Laser Mirror (532, 1064nm) | Coating: |
| 532, 1064 | Design Wavelength DWL (nm): |
| 45 | Angle of Incidence (°): |
| Fused Silica (Corning 7980) | Substrate: <input type="checkbox"/> |
| 15 J/cm ² @ 20ns @ 532nm 20 J/cm ² @ 20ns @ 1064nm | Damage Threshold, Reference: <input type="checkbox"/> |

| | |
|---|------------------------------------|
| Regulatory Compliance | |
| View | Certificate of Conformance: |
| United States | Country of Origin: |
| Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000 | Imported By: |

Product Details

- >99% Reflectivity at Design Wavelengths
- 10-5 Surface Quality for Sensitive Laser Applications
- 532/1064nm, 635-670/1064nm, or 800/1030nm Wavelength Bands
- [TECHSPEC® Nd:YAG Laser Line Mirrors](#) Also Available

TECHSPEC® Dual Band Laser Line Mirrors feature high reflectivity, excellent surface quality, and precision surface flatness to minimize scattering effects. Each coating design has been tested to ensure a high laser damage threshold for compatibility with pulsed laser systems. These fused silica substrate laser mirrors have excellent thermal stability and are available in a variety of standard sizes. TECHSPEC® Dual Band Laser Line Mirrors are ideal for beam steering applications in both laboratory and OEM laser systems. These mirrors are available in a 532/1064nm, 635-670/1064nm, and 800/1030nm dual band coating options for Nd:YAG lasers and red and green guide beams.