

12.5mm Dia. High Contrast UV Polarizer



Stock **#36-650** **3 In Stock**

MRP ₹30,167

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	₹30,167 each
Qty 10+	₹28,754 each
Need More?	Request Quote

Product Downloads

General

Linear Polarizer **Type:**

Physical & Mechanical Properties

11.25 **Clear Aperture CA (mm):**

12.50 **Diameter (mm):**

Thickness (mm):

2.00 ±0.2

Dimensional Tolerance (mm):

+0.0/-0.2

Construction:

Nanoparticle

Clear Aperture (%):

90

Optical Properties

Angle of Incidence (°):

±20

Extinction Ratio:

>100,000:1 (372nm - 388nm)

>10,000:1 (369nm - 390nm)

>1,000:1 (365nm - 395nm)

Substrate: □

Soda Lime Float Glass

Transmission (%):

>51

Transmitted Wavefront, P-V:

< λ/4

Beam Deviation (arcmin):

<1

Polarization Axis Mark (%):

±2

Wavelength Range (nm):

365 - 395

Environmental & Durability Factors

Operating Temperature (°C):

-20 to +80

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

REACH 241:

[Compliant](#)

Country of Origin:

Germany

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Multiple Wavelength Ranges for UV, VIS and NIR
- >100,000:1 Contrast Ratios Available
- Ideal for Use in Harsh Environments

UV, VIS-NIR, and NIR High Contrast Polarizers offer both versatility and performance over a wide range of wavelengths. These polarizers contain uniformly stretched silver nano-particles in a 220 ±25µm thick soda-lime glass laminated on a thicker soda-lime substrate for increased durability. UV, VIS-NIR, and NIR High Contrast Polarizers are ideal for harsh environments, can withstand up to 120°C, are resistant to UV-radiation and chemicals, and can be safely used in humid environments.

Technical Information

