


TECHSPEC® 12.5mm Dia. x 25mm FL, Achromatic Cylinder Lens



Stock **#68-160** **20+ In Stock**

- 1 + MRP ₹37,027

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹37,027 each
Need More?	Request Quote

Product Downloads

General

Cylinder Lens, Achromatic **Type:**

Physical & Mechanical Properties

12.50 +0.0/-0.1 **Diameter (mm):**

±0.2 **Center Thickness Tolerance (mm):**

7.0 **Center Thickness CT 1 (mm):**

Center Thickness CT 2 (mm):

2.0

Optical Properties

Effective Focal Length EFL (mm):

25.00

Substrate:

[N-BK7 / N-SF5](#)

f#:

2.00

Numerical Aperture NA:

0.25

Coating:

MgF₂ (400-700nm)

Wavelength Range (nm):

400 - 700

Back Focal Length BFL (mm):

18.23

Coating Specification:

R_{avg} ≤ 1.75% @ 400 - 700nm

Focal Length Tolerance (%):

±3

Radius R₁ (mm):

10.55

Radius R₂ (mm):

-10.55

Radius R₃ (mm):

-200.14

Surface Quality:

40-20

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Reach 219:

[Compliant](#)

Certificate of Conformance:

[View](#)

Country of Origin:

Japan

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000

Product Details

- Focus Light in Only One Dimension
- Design Minimizes Spherical and Chromatic Aberration
- Ideal for Creating Line Profiles of Broadband Light Sources

Our TECHSPEC® Achromatic Cylinder Lenses are similar in design and function to a standard cylinder lens, but have the added benefit of reducing the spherical and chromatic aberration at the image plane. When used with a monochromatic light source (such as a laser diode), the achromatic cylinder lens will create a 50 – 90% smaller spot, depending on the numerical aperture of the lens. When used with a broadband light source, the lens will minimize chromatic aberration, yielding focused lines with less color separation, or will produce brilliant anamorphic images.

Positive cylindrical lenses are ideal for applications requiring magnification in only one dimension. While spherical lenses focus an incident ray symmetrically, cylindrical lenses act in the same manner but in only one dimension. Typical applications include line generation with laser diodes, focusing a diverging beam onto a linear detector array or using a pair of cylindrical lenses to collimate and circularize the output of a laser diode.

An achromatic cylinder lens is a type of doublet lens consisting of a positive low-index (crown) element and a negative high-index (flint) element cemented together. The two materials are designed to work together to reduce spherical and chromatic aberrations. The additional design freedom provided by using a doublet design allows for further optimization of performance. Therefore, an achromatic lens will have noticeable advantages over a comparable diameter and focal length singlet lens.

Coating Curves