


TECHSPEC[®] 12.5mm Diameter x 20mm EFL Aspherized Achromatic Lens



Aspherized Achromatic Lenses



Stock **#49-659** 20+ In Stock

-

1

+

₹9,653

ADD TO CART

Volume Pricing	
Qty 1-5	₹9,653 each
Qty 6-25	₹7,746 each
Qty 26-49	₹7,084 each
Need More?	Request Quote

Product Downloads

General

Note:

VIS 0° Coating on First Surface, Second Surface is Aspheric Polymer

Type:

Achromatic Lens

Physical & Mechanical Properties	
12.50 +0.00/-0.05	Diameter (mm):
11.00	Clear Aperture CA (mm):
≤5	Centering (arcmin):
6.58	Center Thickness CT (mm):
5.00	Center Thickness CT 1 (mm):
1.58	Center Thickness CT 2 (mm):
5.01	Edge Thickness ET (mm):
Optical Properties	
20.00	Effective Focal Length EFL (mm):
16.07	Back Focal Length BFL (mm):
587.6	Focal Length Specification Wavelength (nm):
13.30	Radius R ₁ (mm):
20.00	Radius R ₂ (mm):
204.48	Radius R ₃ (mm):
N-LAK8 / N-SF57	Substrate: ☐
60-40, glass surface 80-50, polymer surface	Surface Quality:
1.6	f##:
0.31	Numerical Aperture NA:
VIS 0° (425-675nm)	Coating:
R _{avg} ≤0.4% @425 - 675nm	Coating Specification:
425 - 675	Wavelength Range (nm):
Environmental & Durability Factors	
-20°C to 80°C	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 219:
View	Certificate of Conformance:
Japan	Country of Origin:
Edmund Optics India Private Limited	Imported By:



Product Details

- Unique Innovative Design, Low Cost, Color-Corrected Asphere
- Better Color Correction than Standard Achromatic Lenses
- Similar Spherical Aberration Correction to Machined Aspheres
- Prescription Information Available

TECHSPEC® Aspherized Achromats bridge the gap between color-corrected achromats and spherical aberration-corrected aspheres. This unique design results in a cost-effective, color-corrected aspheric component. The doublet lenses consist of two cemented elements matched for their color-correction ability and small RMS spot size. The second surface of the doublet is fused with a molded polymer aspheric surface. These molds create a stable aspheric contour, removing or reducing wavefront errors present in typical achromats while boosting numerical aperture. TECHSPEC Aspherized Achromats' typical applications include fiber optic focusing or collimation, image relay, inspection, scanning, and high numerical aperture imaging.

These lenses were honored with the PhAST/Laser Focus World Innovation Award for Optics and Optical Components.

Technical Information



CT: Center Thickness, ET: Edge Thickness, R: Radius, P: Principal Plane, BFL: Back Focal Length, EFL: Effective Focal Length

Coating Curves

Compatible Mounts