

[See all 227 Products in Family](#)

**TECHSPEC® 12.5mm H x 25mm L x 100mm FL Uncoated, Illumination Grade PCX Cylinder Lens**



Stock **#68-035** **8 In Stock**

- 1 + MRP ₹7,282

**i** Price inclusive of all taxes

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹7,282 each                   |
| Qty 6-25       | ₹6,563 each                   |
| Qty 26-49      | ₹6,228 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

**General**

Cylinder Lens, Plano-Convex **Type:**

**Physical & Mechanical Properties**

2.00 **Center Thickness CT (mm):**

±0.1 **Center Thickness Tolerance (mm):**

|   |  |
|---|--|
| +0.0/-0.2   | <b>Dimensional Tolerance (mm):</b>         |
| 12.5 x 25.0   | <b>Dimensions (mm):</b>                    |
| 1.62  | <b>Edge Thickness ET (mm):</b>             |
| <b>Optical Properties</b>   |  |
| 100.00  | <b>Effective Focal Length EFL (mm):</b>    |
| <a href="#">N-BK7</a>   | <b>Substrate:</b> <input type="checkbox"/> |
| 8   | <b>f#:</b>                                 |
| 0.06  | <b>Numerical Aperture NA:</b>              |
| Uncoated  | <b>Coating:</b>                            |
| 350 - 2200  | <b>Wavelength Range (nm):</b>              |
| 98.66   | <b>Back Focal Length BFL (mm):</b>         |
| ±3  | <b>Focal Length Tolerance (%):</b>         |
| 51.68   | <b>Radius R<sub>1</sub> (mm):</b>          |
| 60-40   | <b>Surface Quality:</b>                    |
| <b>Regulatory Compliance</b>  |  |
| <a href="#">Compliant</a>   | <b>RoHS 2015:</b>                          |
| <a href="#">Compliant</a>   | <b>REACH 201:</b>                          |
| <a href="#">View</a>  | <b>Certificate of Conformance:</b>         |
| China   | <b>Country of Origin:</b>                  |
| Edmund Optics India Private Limited<br>267, Greystone Building, Second Floor,<br>6th Cross Rd, Binnamangala,<br>Stage 1, Indiranagar, Bengaluru,<br>Karnataka, India 560038<br>Phone: +91- 80-6845 0000 | <b>Imported By:</b>                        |

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- N-BK7 Substrate for Broadband Performance
- Cost-Effective for OEM Integration
- Multiple Coating Options Available

TECHSPEC® Illumination Grade PCX Cylinder Lenses are similar to Plano-Convex (PCX) lenses in profile, but include a portion of a cylinder instead of a sphere. These lenses focus light in one dimension and can transform a point of light into a line. TECHSPEC® Illumination Grade PCX Cylinder Lenses are available in circular and rectangular versions, along with multiple coating options. Cylinder lenses are ideal for line projection in machine vision applications or guidance systems.

**Note:** For negative focal length cylinder lenses, see our [TECHSPEC® Illumination Grade PCV Cylinder Lenses](#).



Circular And Rectangular Cylinder Lenses



**PCX Rectangular**