

TECHSPEC<sup>®</sup> 12.5mm Protected Silver Coated, N-BK7 Right Angle Mirror



Stock #89-627 

10 TO 12 DAYS

-

1

+

₹7,941

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| ₹7,941                        |
| Qty 6+                        |
| ₹6,345                        |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Product Downloads

SPECIFICATIONS

General

Right Angle Mirror


Type:

| Physical & Mechanical Properties                                                |                                                       |
|---------------------------------------------------------------------------------|-------------------------------------------------------|
| 12.50                                                                           | Length of Legs (mm):                                  |
| ±0.1                                                                            | Dimensional Tolerance (mm):                           |
| Protective bevel as needed                                                      | Bevel:                                                |
| 15.91 x 11.25                                                                   | Clear Aperture CA (mm):                               |
| 17.70                                                                           | Length of Hypotenuse (mm):                            |
| Optical Properties                                                              |                                                       |
| <a href="#">N-BK7</a>                                                           | Substrate: <input type="checkbox"/>                   |
| 40-20                                                                           | Surface Quality:                                      |
| R <sub>avg</sub> >98% @ 450 - 2000nm<br>R <sub>avg</sub> >98% @ 2000 - 10,000nm | Coating Specification:                                |
| Protected Silver (450-10000nm)                                                  | Coating:                                              |
| Metal                                                                           | Coating Type:                                         |
| ±2                                                                              | Angle Tolerance (arcmin):                             |
| 0.45 - 10                                                                       | Wavelength Range (µm):                                |
| 450 - 10000                                                                     | Wavelength Range (nm):                                |
| 0.5 J/cm <sup>2</sup> @ 532nm & 1064nm, 10ns                                    | Damage Threshold, Reference: <input type="checkbox"/> |
| 1.25                                                                            | Power (fringes) @ 632.8nm:                            |
| 0.50                                                                            | Irregularity (fringes) @ 632.8nm:                     |
| Regulatory Compliance                                                           |                                                       |
| <a href="#">Compliant</a>                                                       | RoHS 2015:                                            |
| <a href="#">View</a>                                                            | Certificate of Conformance:                           |
| <a href="#">Compliant</a>                                                       | Reach 242:                                            |

## PRODUCT DETAILS

- Reflects Light at 90°
  - Ideal for System Alignment
  - Enhanced Aluminum, Protected Gold, and Protected Silver Coatings
- TECHSPEC® Right Angle Mirrors are available with enhanced aluminum, protected gold, or protected silver coatings. These coatings allow for improved handling of the component, increased durability of the metal coating, and protection from oxidation with little impact on the performance of the metal coating. The mirrors are designed with an N-BK7 substrate. Right angle mirrors reflect incident light at 90°, are easily mounted, and are crucial in many optical systems. TECHSPEC® Right Angle Mirrors are ideal for applications requiring precision alignment and high performance.

## TECHNICAL INFORMATION



## COATING CURVES

## CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

---