


[See all 6 Products in Family](#)

## 12.7mm 815nm, Polarizing Cube Beamsplitter



Stock #72-220 [CONTACT US](#)

- 1 + MRP ₹52,569

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹52,569 each
Qty 6+	₹44,710 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Linear Polarizer **Type:**

### Physical & Mechanical Properties

Protective as needed **Bevel:**

>90 **Clear Aperture CA (mm):**

**Construction:**

Cube

**Dimensions (mm):**

12.7 x 12.7 x 12.7 +0.0/-0.3

## Optical Properties

**Beam Deviation (arcmin):**

<3

**Design Wavelength DWL (nm):**

815

**Extinction Ratio:**

>1000:1

**P-Polarization Transmission (%):**

>96

**S-Polarization Reflection (%):**

>99.5

**Substrate:**

Fused Silica

**Surface Flatness (P-V):**

$\lambda/6$  @ 632.8nm

**Surface Quality:**

20-10

**Wavelength Range (nm):**

810 - 825

## Regulatory Compliance

**RoHS 2015:**

**Compliant**

**Certificate of Conformance:**

[View](#)

**Reach 247:**

**Compliant**

**Country of Origin:**

Lithuania

**Imported By:**

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Ideal for Trapped-Ion and Neutral Atom Applications
- Range of Application-Specific Wavelengths from 366nm to 815nm
- Surface Quality of 20-10 to Reduce Loss with Low-Light Signals

Polarizing Cube Beamsplitters for Quantum Computing are ideal for use in trapped ion, linear optical, and neutral atom quantum computing and quantum cryptography and communication applications. These beamsplitters are available in a range of commonly used, application-specific wavelengths across the UV to NIR spectrum covering the main wavelengths of commonly used ions (Ytterbium/Strontium/Calcium) energy levels to provide Rydberg excitation, Doppler cooling and other operations such as Raman effects, trapping of ions and others.

They offer a >99.5% reflection of S-Polarized light and >96% transmission of P-Polarized light. Featuring a compact 12.7mm cube construction, these beamsplitters can be easily integrated into benchtop applications or OEM devices and help to save space in the system. Polarizing Cube Beamsplitters for Quantum Computing feature a fused silica substrate, offering low temperature sensitivity, and are AR-coated for maximum transmission at the design wavelength to ensure optimal performance with low light signals. These beamsplitters feature precision right angle prisms to ensure  $\lambda/6$  surface flatness and a surface quality of 20-10. Half Waveplates for Quantum Computing are also available, and custom wavelengths are available for both.