

TECHSPEC® 12.7mm Dia., 1030nm,  $\lambda/10$  Ultra-Low Reflectivity Window



$\lambda/10$  Ultra-Low Reflectivity Windows

Stock #11-267

CLEARANCE

14 In Stock

-

1

+

₹6,086

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | ₹6,086 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Laser Line Window

Type:

Physical & Mechanical Properties

11.43

Clear Aperture CA (mm):

12.70 +0.00/-0.10

Diameter (mm):

6.35 ±0.20

Thickness (mm):

|                      |                          |
|----------------------|--------------------------|
| <3                   | Parallelism (arcmin):    |
| Protective as needed | Bevel:                   |
| 90                   | Clear Aperture (%):      |
| Fine Ground          | Edges:                   |
| 0.16                 | Poisson's Ratio:         |
| 73                   | Young's Modulus (GPa):   |
| 522.00               | Knoop Hardness (kg/mm²): |

|                                  |                                        |
|----------------------------------|----------------------------------------|
| Optical Properties               |                                        |
| 0                                | Angle of Incidence (°):                |
| Laser Ultra V-Coat (1030nm)      | Coating:                               |
| 1030                             | Design Wavelength DWL (nm):            |
| Fused Silica (Corning 7980)      | Substrate: □                           |
| 1.458                            | Index of Refraction (n <sub>d</sub> ): |
| 10-5                             | Surface Quality:                       |
| 67.8                             | Abbe Number (v <sub>d</sub> ):         |
| R <sub>abs</sub> <0.10% @ 1030nm | Coating Specification:                 |
| λ/10                             | Surface Flatness (P-V):                |
| 15 J/cm² @ 1030nm, 20ns, 20Hz    | Damage Threshold, By Design: □         |

|                                                                   |                                                              |
|-------------------------------------------------------------------|--------------------------------------------------------------|
| Material Properties                                               |                                                              |
| 2.20                                                              | Density (g/cm³):                                             |
| 0.52 (+5 to +35°C)<br>0.57 (0 to +200°C)<br>0.48 (-100 to +200°C) | Coefficient of Thermal Expansion CTE (10 <sup>-6</sup> /°C): |
| 7980 0F                                                           | Fused Silica Grade:                                          |

|                                     |                             |
|-------------------------------------|-----------------------------|
| Regulatory Compliance               |                             |
| Compliant                           | RoHS 2015:                  |
| Compliant                           | Reach 219:                  |
| View                                | Certificate of Conformance: |
| United States                       | Country of Origin:          |
| Edmund Optics India Private Limited | Imported By:                |

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).


## Product Details

- <0.1% ReflectivityLaser Line Coatings

- Nd:YAG and Yb:YAG Wavelength Options
- Reduce Typical Laser System Losses by 3% (Compared to a 0.25% Specified System with 10 Transmissive Optics)
- Increased Transmission Reduces Back Reflections, Ghost Images, and Stray Light

TECHSPEC® *N*/10 Ultra-Low Reflectivity Windows feature anti-reflection coatings with reflection lower than 0.1% at the design wavelength. These windows feature high quality fused silica substrates with *N*/10 surface flatness and 10-5 surface quality to minimize scatter. With ultra-low reflectivity and high damage thresholds, these windows are ideal for integration into laser systems to virtually eliminate surface reflections. TECHSPEC *N*/10 Ultra-Low Reflectivity Windows are available in a range of laser V-Coats from 266nm to 1064nm for compatibility with Nd:YAG and Yb:YAG laser sources. Imperial diameter sizes from 12.7mm to 50.8mm are available.

## Technical Information



## Compatible Mounts