

TECHSPEC® 12.7mm Dia., 355nm T, 532nm R 45° Harmonic Separator



TECHSPEC Nd:YAG Harmonic Separators

Stock #37-718 **20+ In Stock**

⊖ 1 ⊕ MRP ₹22,801

● Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹22,801 each
Qty 6-24	₹20,481 each
Qty 25-49	₹18,262 each
Need More?	Request Quote

Product Downloads

General

Harmonic Beamsplitter **Type:**

Physical & Mechanical Properties

>85 **Clear Aperture (%):**

Construction:

Dichroic	
12.70 +0.00/-0.10	Diameter (mm):
<3	Parallelism (arcmin):
6.35 ±0.20	Thickness (mm):

Optical Properties

45	Angle of Incidence (°):
Coating Specification:	
Surface 1: R _{abs} : >99% @ 532nm, T _{abs} : >95% @ 355nm	
Surface 2: R _{abs} : <0.5% @ 355nm	

532	Reflection Wavelength (nm):
Substrate: <input type="checkbox"/>	
Fused Silica (Coming 7980)	

M10	Surface Flatness (P-V):
10-5	Surface Quality:

355	Transmission Wavelength (nm):
Damage Threshold, Reference: <input type="checkbox"/>	
Surface 1: 5 J/cm ² @ 532nm, 20ns, 20Hz 2.5 J/cm ² @ 355nm, 20ns, 20Hz	
Surface 2: 7.5 J/cm ² @ 355nm, 20ns, 20Hz	

Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 209:

View	Certificate of Conformance:
----------------------	------------------------------------

United States	Country of Origin:
Imported By:	
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

Product Details

- Used to Separate Nd:YAG Harmonic Wavelengths
- Beamsplitter Coating Features >95% Transmission
- M10 Fused Silica Substrate

TECHSPEC® Nd:YAG Harmonic Separators are used to separate the common harmonic wavelengths of an Nd:YAG laser. A beamsplitter coating on the first surface reflects at least one wavelength and transmits another. The second surface of the beamsplitter features an anti-reflective coating to minimize the loss due to reflection. TECHSPEC Nd:YAG Harmonic Separators are available in 45° and 0° angle of incidence options. These harmonic separators are available in multiple wavelength configurations for optimal flexibility in system design.

Note: The Damage Threshold values we publish for this family of products were all tested independently from one another. When using these products with more than 1 incident beam, the resulting Damage Threshold of the system will be negatively impacted.

Compatible Mounts