

[See all 7 Products in Family](#)

TECHSPEC® 12.7mm Dia., 650 - 1050nm, 50R:50T, Ultrafast Beamsplitter



TECHSPEC® Ultrafast Beamsplitters

Stock **#13-833** **20+ In Stock**

1 MRP ₹25,223

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-4	₹25,223 each
Qty 5-9	₹22,398 each
Qty 10-19	₹19,774 each
Need More?	Request Quote

Product Downloads

General

Ultrafast Non-Polarizing Beamsplitter **Type:**

Physical & Mechanical Properties

3.00 ±0.10 **Thickness (mm):**

Diameter (mm):

12.70 +0.00/-0.10

80 **Clear Aperture (%)**

<10 **Parallelism (arcsec)**

Optical Properties

Substrate:
[Fused Silica](#) (Coming 7980)

10-5 **Surface Quality**

45 **Angle of Incidence (°)**

650 - 1050 **Wavelength Range (nm)**

50/50 **Reflection/Transmission Ratio (R/T)**

Coating Specification:
Surface 1:
 $R_{avg} = 50 \pm 3\%$ @ 650 - 1050nm
 $R_p = 35 \pm 3\%$ @ 650 - 1050nm
 $R_s = 67 \pm 3\%$ @ 650 - 1050nm
Surface 2:
 $R_s < 2\%$ @ 650 - 1100nm
 $R_p < 1.5\%$ @ 650 - 1100nm

GDD Specification:
Transmission: $\pm 15 \text{ fs}^2$ @ 650 - 1100nm
Reflectivity: $\pm 15 \text{ fs}^2$ @ 650 - 1100nm

$\lambda/8$ @ 632.8nm **Transmitted Wavefront Distortion:**

$< \lambda/6$ @ 632.8nm **Reflected Wavefront Distortion:**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Lithuania **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000


Product Details

- Designs for Ti:sapphire and Yb:doped Fiber Lasers
- 90:10, 70:30, and 50:50 (R:T) Split Ratios
- Controlled Reflection and Transmission GDD

TECHSPEC® Ultrafast Beamsplitters are designed for use with femtosecond pulsed Ti:sapphire and Yb:doped fiber lasers. Their front surface features a 90:10, 70:30, or 50:50 (R:T) non-polarizing beamsplitter coating while their back surface features an anti-reflective coating to minimize losses due to reflection. Each coating has controlled dispersion to allow for predictable group delay dispersion (GDD) of the transmitted or reflected pulses. TECHSPEC Ultrafast Beamsplitters are available in standard imperial sizes for easy integration into optical systems. Please [contact us](#) if your application requires an Ultrafast Beamsplitter with a custom size or coating specifications.

Note: The arrow on the edge of these optics points towards the beamsplitter coating.

Technical Information



Compatible Mounts

