

TECHSPEC[®] 12.7mm Dia., 650 - 1050nm, 50R:50T, Ultrafast Beamsplitter



TECHSPEC[®] Ultrafast Beamsplitters

Stock **#13-833** **9 In Stock**

-

1

+

₹20,700

ADD TO CART

Volume Pricing	
Qty 1-4	₹20,700 each
Qty 5-9	₹18,360 each
Qty 10-19	₹16,200 each
Need More?	Request Quote

Product Downloads

General	
Ultrafast Non-Polarizing Beamsplitter	Type:
Physical & Mechanical Properties	
3.00 ±0.10	Thickness (mm):
12.70 +0.00/-0.10	Diameter (mm):

80	Clear Aperture (%):
<10	Parallelism (arcsec):
Optical Properties	
Fused Silica (Corning 7980)	Substrate: ☐
10-5	Surface Quality:
45	Angle of Incidence (°):
650 - 1050	Wavelength Range (nm):
50/50	Reflection/Transmission Ratio (R/T):
Coating Specification: Surface 1: R _{avg} = 50±3% @ 650 - 1050nm R _p = 35±3% @ 650 - 1050nm R _s = 67±3% @ 650 - 1050nm Surface 2: R _s <2% @ 650 - 1100nm R _p <1.5% @ 650 - 1100nm	
GDD Specification: Transmission: ±15 fs ² @ 650 - 1100nm Reflectivity: ±15 fs ² @ 650 - 1100nm	
λ/8 @ 632.8nm	Transmitted Wavefront Distortion:
<λ/6 @ 632.8nm	Reflected Wavefront Distortion:

Regulatory Compliance	
View	Certificate of Conformance:
Lithuania	Country of Origin:
Edmund Optics India Private Limited	Importer:


Product Details

- Designs for Ti:sapphire and Yb:doped Fiber Lasers
- 90:10, 70:30, and 50:50 (R:T) Split Ratios
- Controlled Reflection and Transmission GDD

TECHSPEC® Ultrafast Beamsplitters are designed for use with femtosecond pulsed Ti:sapphire and Yb:doped fiber lasers. Their front surface features a 90:10, 70:30, or 50:50 (R:T) non-polarizing beamsplitter coating while their back surface features an anti-reflective coating to minimize losses due to reflection. Each coating has controlled dispersion to allow for predictable group delay dispersion (GDD) of the transmitted or reflected pulses. TECHSPEC Ultrafast Beamsplitters are available in standard imperial sizes for easy integration into optical systems. Please [contact us](#) if your application requires an Ultrafast Beamsplitter with a custom size or coating specifications.

Note: The arrow on the edge of these optics points towards the beamsplitter coating.

Technical Information



Compatible Mounts