

**TECHSPEC® 12.7mm Dia. x 15mm FL, MgF<sub>2</sub> Coated, Achromatic Doublet Lens**



MgF<sub>2</sub> Coated Achromatic Lenses



Stock #49-758 **15 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ ₹6,072

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹6,072 each
Qty 6-25	₹4,827 each
Qty 26-49	₹4,593 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Achromatic Lens **Type:**

**Physical & Mechanical Properties**

**Diameter (mm):**

12.70 +0.0/-0.025	
11.70	Clear Aperture CA (mm):
<1	Centering (arcmin):
8.50 ±0.20	Center Thickness CT (mm):
6.50 ±0.10	Center Thickness CT 1 (mm):
2.00 ±0.10	Center Thickness CT 2 (mm):
5.72	Edge Thickness ET (mm):
Protective as needed	Bevel:

## Optical Properties

15.00	Effective Focal Length EFL (mm):
±1	Focal Length Tolerance (%):
10.56	Back Focal Length BFL (mm):
587.6	Focal Length Specification Wavelength (nm):
10.59	Radius R <sub>1</sub> (mm):
-8.26	Radius R <sub>2</sub> (mm):
-30.70	Radius R <sub>3</sub> (mm):
<a href="#">N-BAF10 / N-SF57</a>	Substrate: <input type="checkbox"/>
40-20	Surface Quality:
1.18	f#:
0.42	Numerical Aperture NA:
MgF <sub>2</sub> (400-700nm)	Coating:
R <sub>avg</sub> ≤1.75% @400 - 700nm	Coating Specification:
1.5λ	Power (P-V) @ 632.8nm:
M4	Irregularity (P-V) @ 632.8nm:
400 - 700	Wavelength Range (nm):

## Regulatory Compliance


<a href="#">Compliant</a>	RoHS 2015:
<a href="#">View</a>	Certificate of Conformance:
<a href="#">Compliant</a>	Reach 240:
China	Country of Origin:
Edmund Optics India Private Limited	Imported By:

## Product Details

- Designed for 0° Angle of Incidence
- Less Than 1.75% Reflectance Per Surface @400 - 700nm
- [VIS 0°](#) and [VIS-NIR](#) Coated Achromats Also Available

TECHSPEC® MgF<sub>2</sub> Coated Achromatic Lenses consist of two optical components cemented together to form an achromatic doublet which is computer optimized to correct for on-axis spherical and chromatic aberrations. These lenses feature a single layer of MgF<sub>2</sub> which provides less than 1.75% reflectivity from 400 – 700nm. TECHSPEC MgF<sub>2</sub> Coated Achromatic Lenses are best for applications involving multi-color (white light) imaging due to their specific doublet lens pairing that enables them to correct the color separation inherent in glass. Having eliminated the problematic chromatic aberrations, achromatic doublet lenses become the most cost-efficient means for polychromatic illumination and imaging.

## Technical Information



## Coating Curves

### Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts

---